







5	PDS: Rev :A	STATUS:Released	Printed: Nov 04, 2015
---	-------------	-----------------	-----------------------


HPCE PART NUMBER (TABLE 3)				
PART NUMBER	TAIL TYPE	ORIENTATION KEY	DIM "A" TAIL LENGTH	DIM "B" RECOMMENDED BOARD THICKNESS
I0137513-001LF	SOLDER	NO	3.17 ±0.25	2.36±0.13
I0137513-002LF	PRESS-FIT	NO	3.17 ±0.25	1.57 MIN



NOTES:

1. CONNECTOR MATERIALS:

HOUSING: HIGH TEMPERATURE THERMAL PLASTIC, BLACK
UL 94V-0 COMPLIANT
CONTACTS: HIGH PERFORMANCE COPPER ALLOY.
2. CONTACT FINISH REF. GS-12-604 SECTION 5.2.
3. PRODUCT SPECIFICATION: GS-12-604.
4. APPLICATION SPECIFICATION: GS-20-128.
5. PRODUCT MARKING ON HOUSING IN AREA SHOWN MEETS FCI SPECIFICATION GS-24-007
6. PACKAGING MEETS FCI SPECIFICATION GS-14-937.
7. ALL HOLE SIZES ARE FINISHED HOLE SIZES.
8. MOUNTING HOLES ARE UNPLATED

Ø 2.40 +/- 0.1 FOR PRESS-FIT TAILS
Ø 2.18 +/- 0.03 FOR SOLDER TAILS
9. PRESS FIT APPLICATION TOOL DRAWING : I0119453.



spec ref			-		dr		Hai-Ling Liu		2015/10/26		projection		MM		size		A2		scale		1:1									
tolerance std			TOLERANCES UNLESS OTHERWISE SPECIFIED			eng		Sunny2 Liu		2015/11/02						ecn no		-		rel level		Released								
ISO 406						chr		Terris Liu		2015/11/02																				
ISO 1101						appr		Pei-Ming Zheng		2015/11/02														product family						
surface 			linear				title		HPCE VERTICAL RECEPT 10LP OMITTED 2LP						dwg no		10137513						rev		A					
																											0.X		±0.5	
																											0.XX		±0.25	
ISO 1302			angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw						sheet 4 of 4											