


THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


| LOC | DIST | REVISIONS |     |                      |         |     |
|-----|------|-----------|-----|----------------------|---------|-----|
|     |      | P         | LTR | DESCRIPTION          | DATE    | DWN |
| AF  | 50   |           | C   | REV PER 0G3H-0076-04 | 23MAR04 | JR  |
|     |      |           |     |                      |         | KR  |



1. SPECIFICATIONS:  
MAGNET WIRE #18 - #34 AWG,  
.040"(.102mm) - .006"(.16mm) DIA.  
OTHER SIZES MAY BE ACCOMMODATED,  
CONSULT TYCO ELECTRONICS FOR APPROVAL.  
LEAD WIRE #20 AWG,  
INSULATED LEAD WIRE.  
MAX INSULATION O.D. .115"(.29MM)  
NO STRIPPING REQUIRED. OTHER  
SIZES MAY BE ACCOMMODATED,  
CONSULT TYCO ELECTRONICS FOR APPROVAL.
2. POCKET RECOMMENDATION:  
CONSULT TYCO ELECTRONICS  
FOR POCKET RECOMMENDATIONS.



ENGINEERS' STANDARD FORM

|                                                                                                                                                                                                                                                                                           |  |                                                                                                                                                                                                                                                                                                                                                                                                             |  |                                     |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------|--|
| -                                                                                                                                                                                                                                                                                         |  | -                                                                                                                                                                                                                                                                                                                                                                                                           |  | -                                   |  |
| -                                                                                                                                                                                                                                                                                         |  | -                                                                                                                                                                                                                                                                                                                                                                                                           |  | -                                   |  |
| -                                                                                                                                                                                                                                                                                         |  | -                                                                                                                                                                                                                                                                                                                                                                                                           |  | -                                   |  |
| Unplated                                                                                                                                                                                                                                                                                  |  | 031-179-000                                                                                                                                                                                                                                                                                                                                                                                                 |  | 4-1601108-1                         |  |
| Unplated                                                                                                                                                                                                                                                                                  |  | 131-180-000                                                                                                                                                                                                                                                                                                                                                                                                 |  | 2-1601108-1                         |  |
| Unplated                                                                                                                                                                                                                                                                                  |  | 131-179-000                                                                                                                                                                                                                                                                                                                                                                                                 |  | 1601108-1                           |  |
| FINISH                                                                                                                                                                                                                                                                                    |  | REFERENCE PART NUMBER                                                                                                                                                                                                                                                                                                                                                                                       |  | TYCO PART NUMBER                    |  |
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                                                                                                                                                                                                    |  | <div><div>DWN<br/>J.WELLER<br/>11JAN2002</div><div>CHK<br/>M.FEHER<br/>11JAN2002</div><div>APVD<br/>K.RANDOLPH<br/>11JAN2002</div></div> <div><div><b>tyco</b><br/><b>Electronics</b></div><div>Tyco Electronics Corporation<br/>Harrisburg, PA 17105-3608</div></div> <div>NAME</div> <div>STD. RANGE WIRE TO EXTENDED 20 AWG.<br/>SEMI-RIGID I.D.C. SIAMEZE TERMINAL<br/>-</div> <div>RESTRICTED TO</div> |  |                                     |  |
| <div>DIMENSIONS:<br/>INCHES</div> <div></div> <div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± .01[0.25]</div><div>3 PLC ± .005[0.13]</div><div>4 PLC ± -</div><div>ANGLES ± 2°</div></div> |  | <div>PRODUCT SPEC<br/>108-2085</div> <div>APPLICATION SPEC<br/>408-8629</div> <div>WEIGHT<br/>-</div> <div>CUSTOMER DRAWING</div>                                                                                                                                                                                                                                                                           |  |                                     |  |
| MATERIAL<br>BRASS, SPRING HARD                                                                                                                                                                                                                                                            |  | SEE TABLE                                                                                                                                                                                                                                                                                                                                                                                                   |  | SCALE 11:1<br>SHEET 1 OF 1<br>REV C |  |