

# CA-06P1N12T0DNS - Cable connector

1619449

<https://www.phoenixcontact.com/us/products/1619449>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, series: CA, angled, shielded: yes, SPEEDCON, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243567



## Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

## Commercial data

Item number	1619449
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAED
Catalog page	Page 90 (C-2-2019)
GTIN	4046356823982
Weight per piece (including packing)	193.3 g
Weight per piece (excluding packing)	193.3 g
Customs tariff number	85366990
Country of origin	DE

# CA-06P1N12T0DNS - Cable connector

1619449

<https://www.phoenixcontact.com/us/products/1619449>



## Technical data

### Product properties

Product type	Circular connector (cable-side)
Data management status	
Article revision	07

### Connector

#### Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overshoot category	III
Degree of pollution	3
Contact diameter <b>Signal contacts</b>	2 mm
Litz wire cross-section <b>Signal contacts</b> max.	2.5 mm <sup>2</sup>
Nominal current per signal contact	20 A

#### Housing

Housing material	Metal
Type of locking	SPEEDCON
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

#### Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

### Environmental and real-life conditions

#### Ambient conditions

# CA-06P1N12T0DNS - Cable connector

1619449

<https://www.phoenixcontact.com/us/products/1619449>



Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

# CA-06P1N12T0DNS - Cable connector


1619449

<https://www.phoenixcontact.com/us/products/1619449>



## Drawings

Schematic diagram



Connector pin assignment

# CA-06P1N12T0DNS - Cable connector

1619449

<https://www.phoenixcontact.com/us/products/1619449>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619449>

cUL Recognized			
Approval ID: E335019-20141210			
Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
48 V	10 A	14 - 14	-

UL Recognized			
Approval ID: E335019-20141210			
Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
48 V	20 A	14 - 14	-

cULus Recognized

# CA-06P1N12T0DNS - Cable connector

1619449

<https://www.phoenixcontact.com/us/products/1619449>



## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-06P1N12T0DNS - Cable connector

1619449

<https://www.phoenixcontact.com/us/products/1619449>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c8424aeb-4e62-4b82-bc98-704eb1e9986e

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)