






Dimension

Dim.A	$(N-1) \times 5.08 + 6.6$
Dim.B	$(N-1) \times 5.08$
Dim.C	$N \times 5.08$

N=Number of poles

Poles	Tolerance
2P - 6P	± 0.15
7P - 12P	± 0.20
13P - 18P	± 0.30
19P - 24P	± 0.40



SECTION P-P

SIGN	DATE	DESCRIPTION	APPROVER
△	11/09'11	Add is cULus	Aaron
△	11/09'11	The Dim C is added	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ㉑ Clamp: Brass Ni plated
- Item ㉒ Terminal (housing): Thermoplastic (UL94V-0)
- Item ㉓ Terminal (Cover): Thermoplastic (UL94V-0)
- Item ㉔ Male contact: PhBz, Tin plated.
- Item ㉕ Terminal screw: Steel Zinc plating " - " slot type
- Item ㉖ Terminal(track): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 12A
- Wire range:
- Solid wire(AWG): 12-30
- Stranded wire(AWG): 12-30
- Torque: 5.2Lb-In.
- Screw: M3
- Wire strip length: 6-7 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C

△ ● Safety Approval:

● Critical dimension:

● Part No.:

V9xx51x2xxxxG

No. OF POLES
02: 2 POLES
03: 3 POLES
:
24: 24 POLES

Color

- 0 Black (RAL9005)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7035/D)
- C Green (RAL6018/U)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V9-5.08 mm Series 2P-24P W/O Flange (Dinrail holder A type)						
PART NO.		V9xx51x2xxxxG			DWG NO.		8V90004	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Aaron 2011.11.09	Tony 2008.01.19			UNIT: mm	X. ±0.50
					SHEET: 01/01		SCALE: NONE	X.X ±0.30
					REV.: C			X.XX ±0.10
								X° ±1°