


KEMET Part Number: M39014/01-1584VTR
(C056T333K5X5CS7301, CKR05BX333KSVTR)

LDD Mil X7R PRF39014, Ceramic, Military/High Reliability, 0.033 uF, 10%, 50 VDC, BX, S (0.001%/1000 Hrs), Lead Spacing = 5.08mm



Dimensions

L	4.826mm +/-0.254mm
H	5.486mm +/-0.254mm
T	2.286mm +/-0.254mm
S	5.08mm +/-0.381mm
LL	31.75mm MIN
F	0.635mm +0.102/-0.051mm
G	0.66mm MIN
K	4.826mm +/-0.254mm

Packaging Specifications

Packaging:	T&R, 305mm, Type I, H0 = 16mm
Packaging Quantity:	2000

General Information

Supplier:	KEMET
Series:	LDD Mil X7R PRF39014
Style:	Radial
RoHS:	No
Prop 65:	WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov .
REACH:	SVHC (Pb - CAS 7439-92-1)
Termination:	Lead (SnPb)
Failure Rate:	S (0.001%/1000 Hrs)
Testing and Reliability:	MIL-PRF-39014
Qualifications:	MIL-PRF-39014
Notes:	Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk

Specifications

Capacitance:	0.033 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Dielectric Withstanding Voltage:	125 V
Temperature Range:	-55/+125C
Temperature Coefficient:	BX
Dissipation Factor:	2.50%
Insulation Resistance:	30.3 GOhms