







PRODUCT NO
10046971-044LF



NOTE:

- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA (ONE SIDE)
MATTE PURE TIN 120u" OVER SOLDERING AREA.
- PACKING SPEC. GS-14-937
- PRODUCT SPEC. GS-12-338.
- MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.

- PART NUMBER 10046971-044LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.
- THE PINS 6, 12, 15, 18, 19, 22, 23, 26, 29, 35 ARE OMITTED.


spec ref	*	dr	Julia Wang	2013/12/18	projection	MM	size	A4	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Julia Wang	2014/03/20			ecn no	-		
ISO 406		chr	-	-			rel level	Released		
ISO 1101		appr	Pei-Ming Zheng	2014/03/20	product family	Power Edge Card				
surface	linear	0.X	±0.50	FCI	title	VERTICAL TYPE	dwg no	10046971-044	rev	A
		0.XX	±0.25	www.fci.com		2X20P(10P OMITTED)				
		0.XXX	±0.13							
ISO 1302	angular	0°	±2°							
					cat. no.	*	Product - Customer Drw	sheet 1 of 2		

Print File - REV C - 2009-06-09


PDS: Rev :A

STATUS:Released

Printed: Apr 01, 2014



—SEE DETAIL A



DETAIL A
SCALE 5.000



VERTICAL TYPE
2X20P(10P OMITTED)

dwg no

10046971-044

rev

A

www.fci.com

cat. no.

1

Product - Customer Drw

sheet 2 of 2