

# CSTLS9M83G56-B0


In Production

Recommended

RoHS

REACH

## Appearance & Shape



## Features

MURATA's ceramic resonator, CERALOCK(R) with built-in load capacitors, has been widely applied as the most suitable component for clock oscillators in a broad range of microprocessors. The CSTLS series can be used in the design of oscillation circuits not requiring external load capacitors, enabling both high-density mounting and cost reduction.

- Features
1. Oscillation circuits do not require external load capacitors. There is some variation in built-in capacitance values applicable to various IC.
  2. Stable over a wide temperature range.
  3. Compact, lightweight and exhibit superior shock resistance performance.
  4. Enable the design of oscillator circuits requiring no adjustment.
  5. Cost-effective and reliable availability.

## Applications

|             |                     |
|-------------|---------------------|
| Other Usage | Consumer/Industrial |
|-------------|---------------------|

## Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B0        | Bulk           | 500                       |

**Attention**

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# CSTLS9M83G56-B0



## Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| Product Type                        | Ceramic Resonator (CERALOCK) |
| Series                              | CSTLS_G                      |
| Frequency                           | 9.830MHz                     |
| Frequency Tolerance                 | +/-0.50% max.                |
| Operating Temperature Range         | -20°C~80°C                   |
| Frequency Shift by Temperature      | -0.40 to +0.20%              |
| Frequency Aging                     | +/-0.20% max.                |
| Resonant Impedance (R1)             | 25ohm max.                   |
| Built-in Load Capacitance (CL1/CL2) | 47pF                         |
| Shape                               | Lead                         |
| Wash                                | Not available                |
| L x W (size)                        | 9.0x6.0mm                    |
| Mass                                | 126mg                        |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.