




SIGN	DATE	DESCRIPTION	APPROVER
△	02/11/09	The design changed	Jacke
△	02/11/09	The design changed to revoke	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Terminal housing:Thermoplastic (UL94V-0)
- Item b Terminal cover:Thermoplastic (UL94V-0)
- Item c Terminal screw:Steel Zinc plating "- "type
- Item d Clamp:Brass, Ni plated
- Item e Female contact:PhBz , Tin plated

Electrical

- Voltage rating: 300V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 4.5Lb-In
- Screw: M3
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

EO xx 01 x 0 xxxx G			
02 2 CONTACTS	0 Black (RAL9005)	0000 Standard @ Logo	RoHS
03 3 CONTACTS	2 Red (RAL3001/D)	000A Standard ANY Logo	Pb<40,000ppm
...	3 Orange(RAL2011/P)	Any special item by	
12 12 CONTACTS	4 Yellow(RAL1018/A)	customer request,	
	5 Green(RAL6018/T)	please contact sales	
	6 Blue (RAL5015/A)	department.	
	8 Grey(RAL7035/D)		

Dim L=N×5.0
Dim B=(N-1)×5.0

Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00
TOL	±0.10				±0.15				±0.20		

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRO PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	EO 5.0 series (A type Ø1.90mm)						
PART NO.	EOxx01x0xxxxG			DWG NO.	8E00001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2009.02.23	Jacke 2009.02.23		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV.: D		X.XX ±0.10
					SHEET: 01/01		X° ±1°