



CT Drawer

TE Internal #: 5-292177-1

Connector Assembly, Plug to Plug Relay Header, Wire-to-Wire, 14 Position, .079 in [2 mm] Centerline, Crimp/IDC, 2 Row, Black, CT Drawer

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug to Plug Relay Header**

Connector System: **Wire-to-Wire**

Number of Positions: **14**

Centerline (Pitch): **2 mm [.079 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug to Plug Relay Header
Connector System	Wire-to-Wire
Sealable	No

Configuration Features

Number of Positions	14
Number of Rows	2

Electrical Characteristics

Operating Voltage	125 V
-------------------	-------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Retention Within Housing	With
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Crimp/IDC
------------------------------------	-----------



Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
Mating Retention	Without
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2 mm[.079 in]

Dimensions

Wire Size	28 – 22 AWG
Row-to-Row Spacing	7.6 mm[.299 in]

Usage Conditions

Operating Temperature Range	-20 – 120 °C[-4 – 248 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	40
Packaging Method	Box & Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 173977-7
CT CONN MT REC ASSY 7P

TE Part # 292177-1
MINI DRAWER CONN FOR CT 14P

Also in the Series | CT Drawer

Wire-to-Board Connector Assemblies
& Housings(4)

Customers Also Bought

TE Part #6609059-2
3EZ1=F7328 S0

TE Part #1375820-2
CST-100 II HOUSING 2 POS

TE Part #6609115-3
1EGG1-2 (NEW GEN=F7642D S0)

TE Part #1-2273111-4
M8 strgt socket to M12 strgt plug AA



TE Part #1-794612-1
PIN CONT 20-24 15 GOLD L/P

TE Part #1969823-1
250 HIGH TEMP POS LOCK HSG FLAG

TE Part #D03269-000
B-155-07-35-22-5

TE Part #1969826-1
250 HIGH TEMP POS LOCK HSG FLAG COVER

TE Part #ANT-W63-MON-RPS
Antenna MON Wifi6/6E Swivel SMA

TE Part #341300-9
PL 250 REC HSG 1P NYLON BLACK

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5-292177-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_5-292177-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5-292177-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Low Power Drawer Connectors QRG

English

Product Specifications

MINI DRAWER CONNECTOR, LEAD FREE VERSION

English

Product Specification

English