

M23 ComLock-S Hood 7-12 mm



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 15 100 0482 |
| Specification | M23 ComLock-S Hood 7-12 mm |
| HARTING eCatalogue | https://b2b.harting.com/09151000482 |

Identification

| | |
|-----------------------------|-------------------------|
| Category | Hoods/Housings |
| Series | Circular connectors M23 |
| Identification | Signal |
| Type of hood/housing | Cable housing |
| Description of hood/housing | EMC version |

Version

| | |
|--------------|-----------------------------|
| Size | M23 |
| Version | Top entry |
| Locking type | ComLock-S rapid locking |
| Details | Compatible to Speedtec (TE) |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition |
| Clamping range | 7 ... 12 mm |

Material properties

| | |
|-------------------------|-------------------|
| Material (hood/housing) | Copper-zinc alloy |
| Surface (hood/housing) | Nickel plated |
| RoHS | compliant |
| ELV status | compliant |

Material properties

| | |
|--------------------------------------|----------------|
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Specifications and approvals

| | |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 5 |
| Net weight | 89.4 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140184053 |
| ETIM | EC003556 |
| eCl@ss | 27440224 Shell for circular connectors |