




SPECIFICATIONS


- Current Rating: 9A AC, DC
- Voltage Rating: 300V AC, DC
- Temperature Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- Contact Resistance: $20\text{m}\Omega$ Max
- Insulation Resistance: $1000\text{m}\Omega$ Min
- Withstanding Voltage: 1500V AC/minute
- Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
1	HC-5557-2x1AW-B-PF-05	---	5.40
2	HC-5557-2x2AW-B-PF-05	4.20	9.60
3	HC-5557-2x3AW-B-PF-05	8.40	13.80
4	HC-5557-2x4AW-B-PF-05	12.60	18.00
5	HC-5557-2x5AW-B-PF-05	16.80	22.20
6	HC-5557-2x6AW-B-PF-05	21.00	26.40
7	HC-5557-2x7AW-B-PF-05	25.20	30.60
8	HC-5557-2x8AW-B-PF-05	29.40	34.80
9	HC-5557-2x9AW-B-PF-05	33.60	39.00
10	HC-5557-2x10AW-B-PF-05	37.80	43.20
11	HC-5557-2x11AW-B-PF-05	42.00	47.40
12	HC-5557-2x12AW-B-PF-05	46.20	51.60

Ordering Information

HC-5557 - N*** - * - PF - 05

Pin Type Colour 默认=透明
Y=孔座 R=红色
L=蓝色 A=直针 B=黑色
AW=弯针 Y=黄色
P=紫色 V=绿色
O=棕色 BR=灰色



GENERAL TOLERANCE

DIM	TOL
X.X	± 0.30
X.XX	± 0.20
X.XXX	± 0.10
Angle	$\pm 3.0^{\circ}$


制图 DRAWING

审核 CHECK
批准 APPROVAL
比例 SCALE
投影 Projection



深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	5557 (4.20) 双排 弯针 黑色	版本 REV.	A
产品料号 PART NO.	HC-5557-2xNAW-B-PF-05	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1



1 初版发行 变更内容 MODIFY CONTENT		日期 MODIFY DATE		GENERAL TOLERANCE		制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuaacantianluELECTRONICS CO., LTD					
				DIM	TOL	审 核 CHECK		产品名称		5557 (4.20) 双排 弯针 Pin 位图		版本 REV.	A
				X. X	±0.30	批 准 APPROVAL		产品料号		HC-5557-2xNAW-B-PF-05		单 位 UNITS	mm
				X. XX	±0.20	比 例 SCALE		投 影				材 料 MATERIAL	
章号 No.				Angle		Projection							
				±3.0°									