


CAVITY SUITABLE FOR
2.8x0.8 thk. FASTON TERMINAL
TE PN 160864-2

- 1 MATERIAL : Acc. EN 60335-1 (incl. glow wire test 750°C without flame), UL 94 V-2
- 2 Location for Part number acc to DIN-1451; 0.2 mm Raised.
- 3 Location for Material Code.
- 4 Location for Tyco Electronics Logo.



SCALE 2:1

A	PA6.6	3POS. HOUSING	0-1987142-2	2
A	PA6 	3POS. HOUSING	0-1987142-1	1
REV.	MATERIAL	DESCRIPTION	PART NUMBER	Sl. No.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN Kishor M 17-Mar-08		 TYCO ELECTRONICS AMP GmbH D-64625.BENSHEIM	
DIMENSIONS: mm		CHK S. Zabeck 17-Mar-08			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.2		APVD Th. Klenner 17-Mar-08		NAME 3 POSITION-HOUSING FOR POSITIVE LOCK RECEPTACLE -	
		PRODUCT SPEC -			
0 PLC $\pm$- 1 PLC $\pm$- 2 PLC $\pm$- 3 PLC $\pm$- 4 PLC $\pm$- ANGLES $\pm 1^\circ$		APPLICATION SPEC -			
MATERIAL - PA6 / PA6.6		FINISH -		SIZE A3	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-1987142	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV A4	