




Wire Protection & Management > Interconnect Devices > Shielded Contacts



Shielded Contact Product Type: **Data Bus Component**
Shielded Contact Wire & Cable Type: **10614 (EMP Hardened), TriAxial**
Shielded Contact Style: **Pin**
Shielded Contact Size: **8**

Features

Product Type Features

| | |
|------------------------------------|--------------------------------|
| Shielded Contact Product Type | Data Bus Component |
| Shielded Contact Wire & Cable Type | 10614 (EMP Hardened), TriAxial |

Contact Features

| | |
|------------------------|-----|
| Shielded Contact Style | Pin |
| Shielded Contact Size | 8 |

Termination Features

| | |
|--------------------|--------|
| Termination Method | Solder |
|--------------------|--------|

Usage Conditions

| | |
|-----------------------------|--------|
| Operating Temperature (Max) | 150 °C |
|-----------------------------|--------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Pb (37% in Solder) <small>Article Safe Usage Statements:</small> |



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

| | |
|---------------------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 750984-004
10612-24-9

Customers Also Bought





TE Part #YDTS26Z23-55PN0000
PLUG ASSY



TE Part #806618-000
214A052-3/42-0




TE Part #814245-000
403A134-3/42-0



TE Part #582693-000
DK-621-1640-4S






TE Part #AFD58-24-31SX-1A
RECP ASSY



TE Part #CN4200-000
55A0131-24-0/2/6



TE Part #326791-000
D-181-2222-90/9CS298



TE Part #109765N002
D-181-3224-90/9CS373



TE Part #832017-000
D-602-0126CS2541



TE Part #1616037-7
DH7BB=RELAY

Documents

Product Drawings

DK-602-0156-3

English

Datasheets & Catalog Pages

Data Bus Components Brochure

English

Product Specifications

Installation Procedure for DK-602-0156 and -0157 Triaxial Contacts

English