

RJ45 connector - VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - 1608016

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)



Push-pull connector (version 14), metal, with 8-pos. RJ45 QUICKON connector insert, with QUICKON fast connection technology, for 26 ... 22 AWG 1-wire and 7-wire conductors, for 5.0 mm ... 8.0 mm cable diameter

Push/pull connector



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 131681
GTIN	4046356131681
Weight per Piece (excluding packing)	68.600 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Standards/specifications	IEC PAS 61076-3-117
Number of positions	8
Connection profile	RJ45
Locking type	Push Pull
Shielded	yes
Insertion/withdrawal cycles	≥ 250
Connection method	IDC fast connection
Conductor cross section	0.13 mm² ... 0.32 mm² (solid)
	0.14 mm² ... 0.36 mm² (flexible)
Connection cross section AWG	26 ... 22 (solid)

RJ45 connector - VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - 1608016

Technical data

Mechanical characteristics

	26 ... 22 (flexible)
Max. cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm
Cable outlet	straight
Color	silver
Degree of protection	IP65/IP67
No. of cable outlets	1
Note	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 3.01, Order No. 2252

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 45 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

Material data

Flammability rating according to UL 94	V0
Housing material	Zinc die-cast
Housing surface material	Nickel-plated
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel
Material	Metal
O-ring material	NBR
Cable seal material	TPE
Material housing intermediate seal	NBR
Height	30 mm

Electrical characteristics

Number of positions	8
Nominal voltage U_N	50 V
Nominal current I_N	1.75 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
GRP transmission properties	CAT5 (IEC 11801:2002) CAT5 (IEC 11801:2002)
Rated current	1.75 A
Overvoltage category	I
Degree of pollution	2
Contact resistance	0.001 Ω (Wire – IDC)

RJ45 connector - VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - 1608016

Technical data

Electrical characteristics

	0.005 Ω (Litz wires – IDC)
Rated voltage (III/3)	72 V (DC)

Standards and Regulations


Standards/regulations	IEC PAS 61076-3-117
Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Push-pull RJ45 connector IP65/67

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440101
eCl@ss 8.0	27440101
eCl@ss 9.0	27440101

RJ45 connector - VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - 1608016

Classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002636
ETIM 6.0	EC002636

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
Nominal voltage UN	50 V		
Nominal current IN	1.75 A		
mm ² /AWG/kcmil	22		

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
Nominal voltage UN	50 V		

RJ45 connector - VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - 1608016

Approvals

Nominal current I _N	1.75 A
mm ² /AWG/kcmil	22

EAC		B.01742
-----	---	---------

cULus Recognized	
------------------	---

Accessories

Accessories

Data cable by the meter

Network cable - VS-OE-OE-93B/... - 1417362



Network cable, PROFINET CAT5 (100 Mbps), 4-position, PVC, green RAL 6018, shielded, free cable end, on free cable end, cable length: Free entry (0.5 ... 400 m)

Panel mounting frame

Panel mounting frames - CUC-V14-F1ZNI-EM/R4O - 1413963



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, for PCB connection, for square panel cutout, with grommet and mounting screws

Stripping tool - VS-CABLE-STRIP-VARIO - 1657407



Stripping tool, for the multi-level stripping of shielded cables

