









		2	3	4	5	6	7	8	
				REV.	ECN NO.	DATE	SIGN	DESCRIPTION	
									
									
									
									
Conn. Pin Assignments Front View				Recommended Panel Cut-Out					
									
				Note: * Ⓞ Important Dimension To Check. * Waterproof Rate: IP68 IP68: 1M Depth Of Water In 24hours * Connector: Nylon+GF, Black * Male Pin: Copper Alloy, Gold Plated * Shell: Zinc Alloy, Nickel Plated. * Nut: Zinc Alloy, Nickel Plated. * O-ring: Silicon, Black * Boardlock: PBT+PC, Black * For Panel Thickness Max. 4.5mm * For PCB Thickness Max. 1.6mm					
UNIT:mm		TITLE M12 DCODE, 90° PANEL 4PIN MCONN MPIN			ITEM NO M12D-04PMMR-SF8001		DRAWN BY Yulong_wang		
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 3:2			DWG NO M12D-04PMMR-SF8001		CHECKED BY Jinhai		
		REV. A			CUSTOMER ALTW		APPROVED BY Jerry		
		WC-REV. A.1					DATE 2016-11-10		
		SHEET 1 OF 1					DATE 2016-11-10		
		QC: Inspection item					DATE 2016-11-10		
Amphenol LTW 安費諾亮泰企業股份有限公司									
								FMW10702-01-02A1	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.