

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 2.5 mm<sup>2</sup>, color: red, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/..-ST, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting: without, type of packaging: packed in cardboard

## Your advantages

- Well-known connection principle allows worldwide use
- Pull-out aid facilitates handling and allows the tensile force to be reduced at the contact point
- Allows connection of two conductors

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1709290                        |
| Packing unit                         | 50 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA03                           |
| Product key                          | AACAGC                         |
| GTIN                                 | 4055626064611                  |
| Weight per piece (including packing) | 6.378 g                        |
| Weight per piece (excluding packing) | 5.814 g                        |
| Customs tariff number                | 85366990                       |
| Country of origin                    | DE                             |

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | PCB connector         |
| Product family        | MSTB 2,5/...-ST       |
| Product line          | COMBICON Connectors M |
| Number of positions   | 3                     |
| Pitch                 | 5.08 mm               |
| Number of connections | 3                     |
| Number of rows        | 1                     |
| Number of potentials  | 3                     |

### Data management status

|                  |    |
|------------------|----|
| Article revision | 00 |
|------------------|----|

### Electrical properties

|                             |       |
|-----------------------------|-------|
| Nominal current $I_N$       | 12 A  |
| Nominal voltage $U_N$       | 320 V |
| Rated voltage (III/3)       | 250 V |
| Rated surge voltage (III/3) | 4 kV  |
| Rated voltage (III/2)       | 320 V |
| Rated surge voltage (III/2) | 4 kV  |
| Rated voltage (II/2)        | 630 V |
| Rated surge voltage (II/2)  | 4 kV  |

### Connection data

#### Connection technology

|                         |                     |
|-------------------------|---------------------|
| Type                    | Standard            |
| Connector system        | COMBICON MSTB 2,5   |
| Nominal cross section   | 2.5 mm <sup>2</sup> |
| Contact connection type | Socket              |

#### Interlock

|                 |         |
|-----------------|---------|
| Locking type    | without |
| Mounting flange | without |

#### Conductor connection

|                                                                       |                                              |
|-----------------------------------------------------------------------|----------------------------------------------|
| Connection method                                                     | Screw connection with tension sleeve         |
| Conductor/PCB connection direction                                    | 0 °                                          |
| Conductor cross section rigid                                         | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross section flexible                                      | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG                                           | 24 ... 12                                    |
| Conductor cross section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

|                                                                                           |                                             |
|-------------------------------------------------------------------------------------------|---------------------------------------------|
| 2 conductors with same cross section, solid                                               | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>   |
| 2 conductors with same cross section, flexible                                            | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.25 mm <sup>2</sup> ... 1 mm <sup>2</sup>  |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Cylindrical gauge a x b / diameter                                                        | 2.8 mm x 2.0 mm / 2.4 mm                    |
| Stripping length                                                                          | 7 mm                                        |
| Drive form screw head                                                                     | Slotted (L)                                 |
| Tightening torque                                                                         | 0.5 Nm ... 0.6 Nm                           |

## Specifications for ferrules without insulating collar

|                           |                    |
|---------------------------|--------------------|
| recommended crimping tool | 1212034 CRIMPFOX 6 |
|---------------------------|--------------------|

## Specifications for ferrules with insulating collar

|                           |                    |
|---------------------------|--------------------|
| recommended crimping tool | 1212034 CRIMPFOX 6 |
|---------------------------|--------------------|

## Material specifications

### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | hot-dip tin-plated                                                               |
| Metal surface terminal point (top layer) | Tin (5 - 7 µm Sn)                                                                |
| Metal surface contact area (top layer)   | Tin (5 - 7 µm Sn)                                                                |

### Material data - housing

|                                                                   |            |
|-------------------------------------------------------------------|------------|
| Color (Housing)                                                   | red (3001) |
| Insulating material                                               | PA         |
| Insulating material group                                         | I          |
| CTI according to IEC 60112                                        | 600        |
| Flammability rating according to UL 94                            | V0         |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850        |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775        |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C     |

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 5.08 mm                                                                              |
| Width [w]           | 15.24 mm                                                                             |

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

|            |         |
|------------|---------|
| Height [h] | 15.5 mm |
| Length [l] | 54.3 mm |

## Notes

|                    |                                                                                                                                                                                          |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 250 V               |
| Rated surge voltage (III/3)                            | 4 kV                |
| minimum clearance value - non-homogenous field (III/3) | 3 mm                |
| minimum creepage distance (III/3)                      | 3.2 mm              |
| Rated insulation voltage (III/2)                       | 320 V               |
| Rated surge voltage (III/2)                            | 4 kV                |
| minimum clearance value - non-homogenous field (III/2) | 3 mm                |
| minimum creepage distance (III/2)                      | 3 mm                |
| Rated insulation voltage (II/2)                        | 630 V               |
| Rated surge voltage (II/2)                             | 4 kV                |
| minimum clearance value - non-homogenous field (II/2)  | 3 mm                |
| minimum creepage distance (II/2)                       | 3.2 mm              |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1709290>

| cULus Recognized<br>Approval ID: E60425-19931011 |                       |                       |                   |                             |
|--------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                      | 250 V                 | 12 A                  | 30 - 12           | -                           |
| Use group D                                      | 300 V                 | 10 A                  | 30 - 12           | -                           |

| VDE approval of drawings<br>Approval ID: 40050694 |                       |                       |                   |                             |
|---------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                   | 250 V                 | 12 A                  | -                 | 0.2 - 2.5                   |

| CSA<br>Approval ID: 13631 |                       |                       |                   |                             |
|---------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B               | 300 V                 | 15 A                  | 28 - 12           | -                           |
| Use group D               | 300 V                 | 10 A                  | 28 - 12           | -                           |

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27460202 |
| ECLASS-12.0 | 27460202 |
| ECLASS-13.0 | 27460202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# MSTB 2,5/ 3-STZ-5,08 RD - PCB connector



1709290

<https://www.phoenixcontact.com/us/products/1709290>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)