

Search within category

GO

BUY NOW

DESIGN / INSTALL



PSN16-M

Parallel Splice, 20 – 16 AWG, nylon insulated, bulk package.

- Specs
- Packaging Details
- Tools
- Documents

★ Add to Favorites

🛒 Add to BOM

Product Type	Loose Piece Splices
Style	Parallel Splice
Wire Range In. (mm²)	20 - 16 AWG (0.75 - 1.5)
Barrel Configuration	Standard
Barrel Type	Seamless
Base Material	Brass
Insulation	Nylon
Panduit Color Code	Blue
Plating Type	Tinned
Part Number Series	PSN
Length In (mm)	0.75 (19.1)
Max. Insulation Diameter In. (mm)	0.15 (3.8)
Wire Strip Length In. (mm)	5/16" (7.9)
Flammability Rating	HB
Max. Voltage Rating	300V
CA-800/EZ Series Crimp Die	—
CA9 Series Crimp Die	—
Tool	CT-100A, CT-1525, CT-2500
CSA Certified	No
UL Listed	No
Packaging Type	Box
Pieces Per Reel	—
Angle	Straight
CE Compliant	No
Part Features	• Designed to splice two solid or stranded wires together to repair or lengthen wires • Parallel design results in only one crimp required to complete splice • Seamless tubular barrel provides a consistent high performance quality crimp
RoHS Compliancy Status	Compliant
Min. Order Qty.	1,000.0000

