

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	08JUL2020	SB	LI

SAFETY ORGANIZATIONS
THIS FILTER WILL BE FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS WILL BE MET:

UL RECOGNIZED* 50A 520V 50Hz/60Hz 40°C
CSA CERTIFIED** 50A 520V 50Hz/60Hz 40°C
*31 JULY 2020 ; **31 AUGUST 2020

OPERATING SPECIFICATION
LINE CURRENT/VOLTAGE: 50A, 520VAC
LINE FREQUENCY: 50/60Hz

MAXIMUM LEAKAGE CURRENT: 8.5mA @ 230VAC, 50Hz
OPERATING AMBIENT TEMPERATURE RANGE @ RATED CURRENT: -25°C TO +40°C

IN AN AMBIENT, T_a, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_o, IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{85 - T_a}{45}}$$

RELIABILITY SPECIFICATIONS
STORAGE TEMPERATURE: -40°C TO +85°C
HUMIDITY: 21 DAYS @ 40°C AND 95% RH

TEST SPECIFICATIONS
INDUCTANCE, NOMINAL: 1.2mH

CAPACITANCE @ 1kHz
LINE TO GROUND, NOMINAL: 1.86µF
NEUTRAL TO GROUND, NOMINAL: 2.2µF
LINE TO NEUTRAL, NOMINAL: 10µF


DISCHARGE RESISTOR
L/L I.R. 2MΩ 1W
L/N I.R. 1MΩ 1W
L/G I.R. 2MΩ 1W
N/G I.R. 1MΩ 1W
IR (NO DISCHARGE RESISTOR) 20°C, 50% RH AND 100VDC, MIN: 6MΩ

RECOMMENDED RECEIVING INSPECITON HIPOT
LINE TO GROUND FOR 1 MINUTE: 2856VDC
LINE TO LINE FOR 1 MINUTE: 2236VDC
LINE TO NEUTRAL FOR 1 MINUTE: 1290VDC

FILTER APPROVAL
THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.

LINE SIDE

LOAD SIDE





SCHEMATIC

TYPICAL INSERTION LOSS
COMMON MODE 50/50Ω; DIFFERENTIAL MODE 50/50Ω

MHz	0.01	0.05	0.15	0.5	1	3	5	10	30
CM	68	65	63	54	49	42	38	32	36
DM	58	52	60	50	43	50	42	38	30

LABEL TO TE MARKING SPECIFICATION



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28FEB2020 SHRICARANA B	 TE Connectivity		
DIMENSIONS: mm		CHK 28FEB2020 LEO IRUDHAYARAJ			
		APVD 28FEB2020 LEO IRUDHAYARAJ			
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	NAME POWER LINE FILTER 50KEPS10BFPW		
0 PLC ±0.5 1 PLC ±0.4 2 PLC ±0.4 3 PLC ±0.130 4 PLC ±0.0500 ANGLES ±0.5		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-4-1609968-7
MATERIAL -		FINISH -	RESTRICTED TO -		
-		CUSTOMER DRAWING	SCALE 1:2 SHEET 1 OF 2 REV B		





© 2020 TE Connectivity. All Rights Reserved.

NOTE 1 GROUND CONNECTION:
DO NOT LOOSEN INNER GROUND NUTS.
TORQUE OUTER TERMINAL SCREWS: 1.2Nm / 10.8 in.lbs
TORQUE GROUND NUTS: 2.5-3Nm

NOTE 2 INPUT OUTPUT CONNECTION TERMINAL
AWG SIZE: 26-8 AWG
WIRE SECTION: 10 mm²
THREADED BOLT SIZE FOR GROUND: M6

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHRICHARANA B 28FEB2020	 TE Connectivity		
DIMENSIONS: mm		CHK LEO IRUDHAYARAJ 28FEB2020			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD LEO IRUDHAYARAJ 28FEB2020	NAME POWER LINE FILTER 50KEPS10BFPW		
0 PLC ±0.5 1 PLC ±0.4 2 PLC ±0.130 3 PLC ±0.0500 4 PLC ±0.0500 ANGLES ±0.5		PRODUCT SPEC -	SIZE A300779		
MATERIAL -		APPLICATION SPEC -	CAGE CODE C-4-1609968-7		
FINISH -		WEIGHT -	DRAWING NO C-4-1609968-7		
CUSTOMER DRAWING		SCALE 1:2		SHEET 2 OF 2	REV B