


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW DRAWING	18JUN2014	GB	SzN
	B1	DIM.TOLERANCE CORRECTION	07OCT2016	GB	SzG
	B2	PCN-24-203287 - OBSOLETE	06AUG2024	GB	SzN



Max.0.2mm Grat an Formtrennung, Anguss und Ausstosser zulaessig
MAX.BURRS 0.2MM PERMITTED ON MOULD SPLIT LINE, INJECTION AND EJECTION MARKS

1:1

PRODUCT CHARACTERISTICS ACC. QMP EMEA-12 BESONDERE MERKMALE NACH QMP EMEA-12		TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-140@D. CENTRIC TO NOMINAL DIMENSION. UNIFORM 1982-11 SHALL APPLY. Freimasstoleranzen nach DIN 16901-140@D. Es gilt die Ausgabe 1982-11.	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG 18JUN2014 CHK Gergely Benczur 18JUN2014 APVD Szilard Nemes 18JUN2014	
DIMENSIONS: (mm)		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1° FINISH	
MATERIAL PA 6.6 GF30		PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	
Blende 7/15/33 SVDO Screen 7/15/33 SVDO		NAME SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C=1437284-1 -	
SCALE 2:1 SHEET 1 OF 1 REV B2			