






A
B
C
D
E
F


Customer Drawing



M方向键位示意图
Key Abridged General View of M Direction



端子
Terminal



Note:

Mechanical loads applied to the connector must be controlled by appropriate strain relief of the cable. No bend/twist/flex is allowed on cable prior to securement. Cable must be fixed to a point structurally contiguous with the receptacle connector within 75mm Max. from the mating interface of the plug and receptacle. No relative movement between receptacle and first cable securing device is permissible. Strain relief distance should be minimized for all applications

规格参数 (Spec.):


1. 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$.
2. 额定电流 Current rating (connector only):
6mm²: 45A, 10mm²: 60A.
3. 额定电压 Operating voltage: 1000 VDC.
4. 耐电压 Dielectric withstanding voltage: 5000 VDC.
5. 防护等级 Protection class: IP67 & IP2X.
6. 电磁屏蔽 Shielding.
7. 机械寿命 Mating cycle: 100 Min.
8. 带自动二次锁扣 Automatic secondary lock.
9. 带高压互锁 Electrical interlock (HVIL).
10. 对配插座见图纸 Mating receptacle see drawing: "PL082-60".

订购信息 Ordering Information

PL18		2	X	-	6	1	-	10
键位及颜色 Key & Color			高压互锁 HVIL			线缆大小 Cable Size		
"X", 橙色 Orange			0, 不带互锁 No HVIL			"10"=10mm ² shielding		
"Y", 黑色 Black			1, 带互锁 With HVIL			"6"=6mm ² shielding		
"U", 黄色 Yellow								



REVIEWS			REVISIONS			
REV	ZONE	ECO	DESCRIPTION	DATE	BY	APPR
1	--	--	INITIAL RELEASE	11/21/13	RW	EC
A1	--	--	Updated Spec.	07/17/14	RW	EC
A2	--	--	Updated Back Cover	11/21/14	RW	EC
B	--	--	Change The Color of Press Key & Recommended Wire OD	03/04/15	RW	EC
B1	--	--	Add dimension of terminal	04/28/15	RW	EC
C	--	--	Add key abridged general view	09/17/15	RW	TS
D	--	--	Change pin for 4mm2 wire	11/03/15	RW	TS
E	--	--	Updated Spec.	11/08/16	SW	TS
F	--	--	Add Suggestion For Mounting and Installation	06/28/17	JL	JG
G	--	--	Add rating current	02/07/18	YM	JG
H	--	--	Updated Spec.	08/24/18	Fred	JL



Standard Part List (With HVIL)带高压互锁

P/N	Model NO.	Recommended Wire OD	Dimension "A"	Mating Rcpt Model NO.
AC-HA000925	PL182X-61-6	6.4~7.0mm	ø5.80mm	PL082X-61-6
AC-HA000926	PL182Y-61-6			PL082Y-61-6
AC-HA000927	PL182U-61-6			PL082U-61-6
AC-HA001076	PL182X-61-10	8.3~8.9mm	ø7.40mm	PL082X-61-10
AC-HA001077	PL182Y-61-10			PL082Y-61-10
AC-HA001078	PL182U-61-10			PL082U-61-10

Standard Part List (Without HVIL)不带高压互锁

P/N	Model NO.	Recommended Wire OD	Dimension "A"	Mating Rcpt Model NO.
AC-HA000928	PL182X-60-6	6.4~7.0mm	ø5.80mm	PL082X-60-6
AC-HA000929	PL182Y-60-6			PL082Y-60-6
AC-HA000930	PL182U-60-6			PL082U-60-6
AC-HA001079	PL182X-60-10	8.3~8.9mm	ø7.40mm	PL082X-60-10
AC-HA001080	PL182Y-60-10			PL082Y-60-10
AC-HA001081	PL182U-60-10			PL082U-60-10

AMPHENOL TP		Amphenol Technical Products International Asia.				
		第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE
签 名 SIGNATURE		日期 DATE	UNLESS OTHERWISE SPECIFIED			PART NAME:
制 图 DRAWN		Fred	1) All dimensions are in metric(mm). 2) Tolerances are as follows:			PwrLok 4mm 2POS Plug Conn
审 核 CHECKED			0 PL DEC ±1.00 1 PL DEC ±0.50 2 PL DEC ±0.20			DWG NO:
批 准 APPROVAL			Angles ±1°			PL182-60
						CUST PART #:
						N/A
						CUST REV.
						-