

Specification for Approval

Customer: _____

Customer P/N: _____

EEC P/N: SG24301N0

Spec No.: _____

Version No.: V0.1

Description: 100/1000 BASE-T

Customer Approval		EEC Approval	
Inspected By:		Issued By:	Duffy
Checked By:		Checked By:	/
Approved By:		Approved By:	Jerry
Approved Date:		Issued Date:	2024/7/2


Please Return One Copy to Us After Approved,TKS! (承认后请回寄一份,谢谢)

- Remark:
- 1. Before use, please confirm whether this product is suitable for your design, Scientific only ensure products meet this specification.
 - 2. This specification data change must be confirmed by both parties,any individual modification is invalid.
 - 3. If customer placed orders without signing back this specification, it is regarded as recognition.




绵阳敦源电子科技有限公司
Mianyang Dunyuan Electronics Technology Co.,Ltd
地址：四川省绵阳市高新区综合保税区
ADD: Comprehensive Bonded Zone, High-Tech Industrial Development Zone Mianyang, SiChuan

A. MECHANICAL(unit:mm)



B. Schematics




DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
100/1000 BASE-T	SG24301N0		PAGE: 2/4

C. ELECTRICAL SPECIFICATIONS @25°C

Unless Otherwise Specified, Testing is Performed at 25°C ± 5°C

1. OCL: 350uH Min @ 100KHz, 0.1V
2. Leakage Inductance: 0.5uH Max @ 100KHz, 0.1V
3. DCR: 1400mΩ Max
4. Turns Ratio: 1CT:1CT±5%
5. Insertion Loss: -1.1 dB Max @ 1-100 MHz
6. Return Loss: -18 dB Min @ 1-30 MHz
 - 14.4 dB Min @ 40 MHz
 - 13.1 dB Min @ 50 MHz
 - 12 dB Min @ 60-80 MHz
 - 10 dB Min @ 100 MHz
7. Cross Talk: -30 dB Min @ 1-100 MHz
8. Common Mode Rejection: -30 dB Min @ 1-100 MHz
9. Isolation Hipot: 1500VAC 1mA 60S
10. Operating temperature 0°C to +70°C
11. Storage temperature -40°C to +85°C

D. RECOMMEND REFLOW SOLDERING CURVE

MSL:

Grade: 1 level. Floor life: 0.5 year Condition: ≤30°C/60%RH.




Ramp up rate=3°C/s max Ramp down rate=6°C/s max

TL=217°C tL=60s-150s Tp=250+/-3°C Time within 5°C of actual Peak Temperature (tp): 20~40s

Ts min=150°C Ts max=200°C Ts min to Ts max: 60s-180s, 25°C to peak Temperature: 8minutes max

DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
100/1000 BASE-T	SG24301N0		PAGE: 3/4

E. Packaging specification



Package Quantity:

One Reel=1500Pcs

One Inner Carton=1500*2=3000Pcs

One Export Carton=3000*2=6000Pcs

DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
100/1000 BASE-T	SG24301N0		PAGE: 4/4