

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier



1425595

<https://www.phoenixcontact.com/us/products/1425595>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 5-position, Socket, straight, M12, coding: L, PCB mounting, THR solder connection

Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in

Commercial data

Item number	1425595
Packing unit	60 pc
Minimum order quantity	60 pc
Note	Made to order (non-returnable)
Sales key	AB23
Product key	ABQAGW
GTIN	4055626427263
Weight per piece (including packing)	5.088 g
Weight per piece (excluding packing)	5.088 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier



1425595

<https://www.phoenixcontact.com/us/products/1425595>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Notes on operation	FE not connected to metal parts that can be touched, no protective function

Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	5
Seal present	yes
Coding	L
Thread type	M12

Insulation characteristics

Ovvoltage category	III
Degree of pollution	3

Data management status

Article revision	03
------------------	----

Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage U_N	63 V
Nominal current I_N	16 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Power
----------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 4T

Connector

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier



1425595

<https://www.phoenixcontact.com/us/products/1425595>

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	L

Cable/line

Signal type/category	Power
----------------------	-------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

Environmental and real-life conditions

Ambient conditions	
Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)

Standards and regulations

M12	
Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111
Note	In line with

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Tray
Delivery state	with assembly pad

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier




1425595

<https://www.phoenixcontact.com/us/products/1425595>

Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier



1425595

<https://www.phoenixcontact.com/us/products/1425595>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1425595>

cULus Recognized				
Approval ID: E468743-20180113				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	63 V	16 A	-	-

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier



1425595

<https://www.phoenixcontact.com/us/products/1425595>

Classifications

ECLASS

ECLASS-13.0	27440223
-------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FSL-4FE-L180 THR GR T - Contact carrier



1425595

<https://www.phoenixcontact.com/us/products/1425595>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com