


[Have a Question?](#)


Chat with a Product Information Specialist



What can we help you find?



6-5175710-5 Product Details


6-5175710-5

TE Internal Number: 6-5175710-5



Active

.050 Series Board Mount Connectors



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Connector Style = Receptacle
- 20 Positions
- PCB Mounting Orientation = Vertical
- Termination Method to PC Board = Through Hole - Solder

[View all Features](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- PCB Mounting Orientation = Vertical
- PCB Mount Retention = With
- PCB Mount Retention Type = Retention Solder Tails
- [PCB Mount Alignment](#) = Without
- [Shell Type](#) = All Plastic
- [Product Series](#) = Series I

Termination Features:

- Termination Method to PC Board = Through Hole - Solder
- [Termination Post Length \(mm \[in\]\)](#) = 3.10 [0.122]

Body Features:

- Mating Retention = Without
- Post Plating = Tin over Nickel

Contact Features:

- [Contact Plating, Mating Area, Material](#) = Gold (30)
- Contact Base Material = Phosphor Bronze

Housing Features:

- Connector Style = Receptacle
- Mating Alignment = Without
- Centerline (mm [in]) = 1.27 [0.050]
- Housing Material = Thermoplastic - GF
- Housing Color = Black

Configuration Features:

- [Number of Positions](#) = 20
- [Shielded](#) = No

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [UL Flammability Rating](#) = UL 94V-0

Other:

- Brand = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



