





PRODUCT NO
10046971-015LF



NOTE:





1. Material:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA.(ONE SIDE)
Matte Tin 120u" OVER SOLDERING AREA.)
2. PACKING SPEC. GS-14-937
3. PRODUCT SPEC. GS-12-338.
4. MANUFACTURE'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.

5. PART NUMBER 10046971-015LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A
WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.



spec ref	*	dr	Eric Jiang	2013/09/26	projection	MM	size	A4	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	De-Ming Lu	2014/05/12			ecn no	-		
		chr	-	-			rel level	Released		
		appr	Pei-Ming Zheng	2014/05/12	product family	Power edge card				
surface	linear	0.X	±0.5		title	VERTICAL TYPE (17PX2)	dwg no	10046971-015	rev	A
		0.XX	±0.25			POWER EDGE CONNECTOR OF				
		0.XXX	±0.13							
	angular	0°	±2°		cat. no.	*	Product - Customer Drw	sheet 1 of 2		

PRODUCT NO
10046971-015LF



DETAIL A
SCALE 5.000

RECOMMENDED PC BOARD LAYOUT
AND THE THICKNESS IS 2.36mm

dr	Eric Jiang	2013/09/26	projection	MM	size	A4	scale	1.000	
eng	De-Ming Lu	2014/05/12			ecn no	-			
chr	-	-			rel level	Released			
appr	Pei-Ming Zheng	2014/05/12	product family		Power edge card				
		title			VERTICAL TYPE (17PX2)		dwg no		rev
					POWER EDGE CONNECTOR OF		10046971-015		A
www.fci.com		cat. no.		*	Product - Customer Drw			sheet 2 of 2	