

CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1 mm² ... 1 mm², AWG 18

Commercial data

Item number	1674888
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	BF7AIA
Catalog page	Page 507 (C-2-2019)
GTIN	4017918135584
Weight per piece (including packing)	0.65 g
Weight per piece (excluding packing)	0.65 g
Customs tariff number	85366990
Country of origin	DE

CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

Technical data

Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
---------	--

Mounting

Assembly note	At voltages of < 5 V and currents < 5 mA, gold-plated contacts are recommended.
	The quality of a crimp connection is determined by DIN EN 60352-2.

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
	HC-M-08-MBIT
Type	Individual male contact
Contact material type	turned

Data management status

Article revision	03
------------------	----

Connection data

Connection method	Crimp connection
Contact connection type	Pin
Connection technology	Crimp connection
Conductor cross section	1 mm² ... 1 mm²
Connection cross section AWG	18
Stripping length of the individual wire	8 mm
Conductor cross section flexible	0.75 mm² ... 1 mm²

Material specifications

Contact material	Copper alloy
Contact surface material	gold-plated

CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

Dimensions

Mechanical characteristics

Contact diameter	1.6 mm
------------------	--------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ED-1,00ST AU - Crimp contact


1674888

<https://www.phoenixcontact.com/us/products/1674888>



Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-1,00ST AU - Crimp contact

1674888

<https://www.phoenixcontact.com/us/products/1674888>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674888>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1c5e6875-8234-4d20-90a6-495f5eab5cca

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com