






PART NUMBER 10046971-051LF




- NOTE:
- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
 - PACKING SPEC. GS-14-937
 - PRODUCT SPEC. GS-12-338.
 - MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.
 - PART NUMBER 10046971-051LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A
WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.
 - THE PINS 6,7,13,14,25,26,32,33 ARE OMITTED.

spec ref		*	dr Jackie Huang		2015/02/11	projection		MM	size	scale
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED	eng Hai-Ling Liu		2015/04/06				A2	3:1
ISO 406			chr Terris Liu		2015/04/06	ecn no	Released			
ISO 1101			appr Pei-Ming Zheng		2015/04/06			product family		
surface	linear	0.X	±0.5		title	PEC V/T STB	2x19P 8P OMITTED	dwg no	10046971-051	rev
		0.XX	±0.25							
		0.XXX	±0.100							
	angular	0°	±2°	www.fci.com						




RECOMMENDED EDGE CARD LAYOUT



RECOMMENDED HOST BOARD LAYOUT



Copyright FCI.

spec ref		*	dr Jackie Huang		2015/02/11	projection  MM	size A2	scale 2:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED	eng Hai-Ling Liu		2015/04/06		← →	ecn no	rel level Released	
ISO 406			chr Terris Liu		2015/04/06					
ISO 1101			appr Pei-Ming Zheng		2015/04/06					product family
surface			title		PEC V/T STB					dwg no 10046971-051
ISO 1302		linear	0.X ±0.5		2x19P 8P OMITTED					
			0.XX ±0.25							
			0.XXX ±0.100							
ISO 1302		angular	0° ±2°	www.fci.com		cat. no.		Product - Customer Drw		sheet 2 of 2