

# AI 1 - 8 RD-GB - Ferrule



1208982

<https://www.phoenixcontact.com/us/products/1208982>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, color: red

## Your advantages

- Due to the increased diameter of the insulating collar, this type of ferrule is specifically used with AWG cables
- These ferrules enable practical crimping of conductors with increased insulation

## Commercial data

Item number	1208982
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	BH34
Product key	BH341S
Catalog page	Page 484 (C-3-2019)
GTIN	4046356130400
Weight per piece (including packing)	0.097 g
Weight per piece (excluding packing)	0.097 g
Customs tariff number	85369010
Country of origin	DE

# AI 1 - 8 RD-GB - Ferrule



1208982  
<https://www.phoenixcontact.com/us/products/1208982>

## Technical data


### Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Data management status	
Article revision	06

### Connection data

Conductor connection	
Conductor cross section flexible max.	1 mm²
Conductor cross section AWG max.	18
Stripping length	11 mm

### Dimensions

Dimensional drawing	
Sleeve length	8 mm
Maximum stripping length	11 mm
Ferrule diameter	1.5 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.3 mm
Inner dimensions of the insulating collar	3.4 mm

### Material specifications

Color	red (RAL 3001)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	tin-plated (galvanic)
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

Technical data	
Sleeve length	8 mm

### Environmental and real-life conditions

Ambient conditions	
Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)

# AI 1 - 8 RD-GB - Ferrule



1208982

<https://www.phoenixcontact.com/us/products/1208982>


Short-term temperature	120 °C
------------------------	--------

## Standards and regulations

Design according to standard	UL 486F-E
------------------------------	-----------

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI 1 - 8 RD-GB - Ferrule

1208982

<https://www.phoenixcontact.com/us/products/1208982>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1208982>



**cULus Listed**

Approval ID: E488001

# AI 1 - 8 RD-GB - Ferrule



1208982

<https://www.phoenixcontact.com/us/products/1208982>

## Classifications

### ECLASS

ECLASS-11.0	27400201
ECLASS-13.0	27400201
ECLASS-12.0	27400201

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# AI 1 - 8 RD-GB - Ferrule

1208982  
<https://www.phoenixcontact.com/us/products/1208982>



## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)