









Copyright FCI.

PRODUCT NO
10046971-046LF



SECTION E-E
SCALE: 2.000
BOARD RETENTION PINS

- NOTE:
1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA (ONE SIDE)
MATTE TIN 120u" OVER SOLDERING AREA.
2. PACKING SPEC: GS-14-937
3. PRODUCT SPEC: GS-12-338.
4. MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.

5. PART NUMBER 10046971-046LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS
IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.
6. THE PINS 4 TO 14, 17 TO 22, 29 TO 34, 37 TO 47 ARE OMITTED.

spec ref	*	dr	Julia Wang	2014/02/13	projection	MM	size	A4	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	De-Ming Lu	2014/02/26			ecn no	-	rel level	Released
ISO 406		chr	-	-	product family	Power edge card	rel level	Released		
ISO 1101		appr	Pei-Ming Zheng	2014/02/26						
surface	linear	0.X	±0.50	FCI	title	VERTICAL TYPE	dwg no	10046971-046	rev	A
		0.XX	±0.25	www.fci.com		2X25P (OMITTED 34P)				
		0.XXX	±0.13							
ISO 1302	angular	0°	±2°							
					cat. no.	*	Product - Customer Drw	sheet 1 of 2		

