

SPECIFICATION FOR APPROVAL

规格书

Customer (客户名称):

Customer P/N(客户编号):

Our P/N (本厂编号):

FS2514NB0808-H6.0-R01

Approval Date(日期):

2024.10.25

Environment Request(环境标准):

☐ Non-RoHS (非 RoHS 标准)

☒ RoHS (RoHS 标准)

☐ REACH (REACH 标准)

☐ Others (其他)

CUSTOMER'S APPROVED SIGNATURE



泰州福声电子科技有限公司

Taizhou Fusheng Electronic Technology Co.,Ltd.

Adds: No.98 of FengHuang Road West,Hailing District ,Taizhou .

地址: 江苏省泰州市海陵区凤凰西路 98 号

Tel: +86-523-86219066

Fax: +86-523- 81601108

[Http://www.tzfsdz.com](http://www.tzfsdz.com)

E-mail: fs.wu@electronic-tech.cn

	DESINGER	CHECKED	APPROVED
SIGNATURE			
DATE			

Alteration History

变更历史


Note 序号	Date 日期	Detail changes 变 更 内 容	Reason 变更理由	Revision 变更表示

Speaker Specification

Part No.	Customer No 客户型号		Customer code 客户编号	
	Our Part No 本厂编号	FS2514NB0808-H6.0-R01		Revision 版本 A
No.	Item 项目	Specification 规格	Testing Condition 测试条件	
1.	Rated Imp 共称阻抗	8Ω±15%	At 2kHz 1.0Vrms	
2.	Resonance Freq 最低共振周波数	1050Hz±20%	Without Baffle	
3.	Output S.P.L. 出力音压	84±3dB	At 0.1m 0.1w 0.8~5.0KHz Average	
4.	Rated Power 定格入力	at 0.8W	at 2.53Vrms	
5.	Max Power 最大入力	at 1.2W	at 3.1Vrms	
6.	Frequency Range 实效频宽	600~12kHz		
7.	Operation 可靠性试验	Must Be Normal at Rated Frequency Range	ProgramSource0.8W FO~10kHz	
8.	Buzzes & Rattles 异常音试验	Should not be audible buzz and rattle at Rated Frequency Range 无异常声	Sine Wave Between (正弦波入力) at 2.53Vrms / FO---- 10kHz	
9.	T H D 失真	10% Max	Rated Power Input 1000Hz	
10.	Magnet 磁铁	NdFeB		
11.	Operating Temperature 动作温度	-30℃ to +35℃		
12.	Storage Temperature 储存温度	-40℃ to +65℃		
13.	Weight 重量	g/PC		


14.	Cold Test 耐寒试验	Must be normal after having been in a test chamber for 96 hours at the condition of $-40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and then left 2 hours in a room. ($-40^{\circ}\text{C} \pm 2^{\circ}\text{C}$, 96 小时试验室温两小时后,无异常)
15.	Heat Test 耐热试验	Must be normal after having been in a test chamber for 96 hours at the condition of $+65^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 90~95% R.H and then left 2 hours in a room. ($+65^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 90~95% R.H 96 小时试验, 常温 2 小时后,无异常的不良)
16.	Load Test 连续负荷试验	Must be normal after load test :white noise 0.8W 96 hours. At rated frequency range (白噪音 0.8W 连续 96 小时试验后无异常的不良)
17.	Short Term Max Power test 瞬間最大功率试验	Test for 1 hour under maximum power. Input shall be white noise in rated frequency response. And the signal will be 1 second on, 59 seconds off, total 60 cycles at rated frequency range, Must be normal after the test (白噪音 1.2W, 1 秒开 59 秒关, 连续 60 回合, 试验后无异常之不良)
18.	Drop Test 跌落试验	Drop the speakers contained in normal box onto a board 5mm thick 6 times from a height of 1.0m . Must be normal after the test (在厚 5mm 的木板上从 1.0m 的高度跌落 6 次,无异常不良)

Temperature Cycle Test(5 cycle)





Frequency Response




频响曲线



阻抗曲线



Product Outside View



注: 1. 标示“*”为重点检测尺寸;

2. 未有说明，则默认图示 LCCO；

3. 未注公差: $\pm 0.2\text{mm}$

泰州福声电子科技有限公司



Title: FS3018NB0408-H3.7-R01

						版本	Y0
						DATE	
SYM	REV'S IOW	NAME	DATE	SCALE	1:1	QUANTITY	I
						QUANTITY	I
						DRAW	CHECK
							APPROVE

Title: FS3018NB0408-H3.7-R01