


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C	REVISED PER ECR-06-010412	31OCT06	HMR	KR

D




- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59 ± 0.08 $[\cdot 220 \pm \cdot 003]$ CENTERS.
- SLOT ACCEPTS A SINGLE WIRE MAX OF $0.64 - 0.81\text{mm}$ $[\#22 - \#20]$ AWG COPPER MAGNET WIRE.
- AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.


C



B



A



D

C

1217128

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 23NOV1998	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608				1217128-1	
DIMENSIONS: mm [INCHES]		CHK PHILLIP M. FORTNEY 23NOV1998					PART NUMBER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PETE DESANTIS 23NOV1998	NAME TAB, 4.75 $[\cdot 187]$ FASTON, TM 300 SERIES MAG-MATE TM				1217128-1	
0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm 0.25[\cdot 010]$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$		PRODUCT SPEC 108-2012 APPLICATION SPEC 114-2046	SIZE A2				CAGE CODE 00779	
MATERIAL 082 PRE-MILLED BRASS		FINISH 0.002032 $[\cdot 000080]$ MIN TIN	DRAWING NO C=1217128				RESTRICTED TO -	
CUSTOMER DRAWING		WEIGHT -	SCALE 10:1				SHEET 1 of 1	
			REV C					