

Description:

This N-Channel and P-Channel MOSFET use advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.


It can be used in a wide variety of applications.

Features:

N-Channel: $V_{DS}=60V, I_D=16A, R_{DS(on)}<36m\Omega @V_{GS}=10V$

P-Channel: $V_{DS}=-60V, I_D=-18A, R_{DS(on)}<90m\Omega @V_{GS}=-10V$

- 1) Low gate charge.
- 2) Green device available.
- 3) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 4) Excellent package for good heat dissipation.



Absolute Maximum Ratings: ($T_C=25^\circ C$ unless otherwise noted)

Symbol	Parameter	N-Channel	P-Channel	Units
V_{DS}	Drain-Source Voltage	60	-60	V
V_{GS}	Gate-Source Voltage	± 20	± 20	V
I_D	Continuous Drain Current- $T_C=25^\circ C$	16	-18	A
	Continuous Drain Current- $T_C=100^\circ C$	12	13	
	Pulsed Drain Current	70	-75	
P_D	Power Dissipation	23	23	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150		$^\circ C$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case ²	6	$^\circ C/W$

Package Marking and Ordering Information:

Part NO.	Marking	Package
DOD603	D603	TO-252-4

N-CH Electrical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourctce Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	60	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =60V	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 20V, V _{DS} =0A	---	---	± 100	nA
On Characteristics ^{.(Note 3)}						
V _{GS(th)}	GATE-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	1	1.6	3	V
R _{DS(ON)}	Drain-Source On Resistance	V _{GS} =10V, I _D =10A	---	26	36	m Ω
		V _{GS} =4.5V, I _D =5A	---	36	45	
Dynamic Characteristics ^{.(Note4)}						
C _{iss}	Input Capacitance	V _{DS} =25V, V _{GS} =0V, f=1MHz	---	1100	---	pF
C _{Oss}	Output Capacitance		---	52	---	
C _{rss}	Reverse Transfer Capacitance		---	45	---	
Switching Characteristics ^{.,(Note4)}						
t _{d(on)}	Turn-On Delay Time	V _{DD} =30V, R _{GEN} =1.8 Ω I _D =15A, V _{GS} =10V	---	7.6	---	ns
t _r	Rise Time		---	20	---	ns
t _{d(off)}	Turn-Off Delay Time		---	15	---	ns
t _f	Fall Time		---	24	---	ns
Q _g	Total Gate Charge	V _{GS} =10V, V _{DS} =30V, I _D =10A	---	20.3	---	nC
Q _{gs}	Gate-Source Charge		---	3.7	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	5.3	---	nC
Drain-Source Diode Characteristics						

V_{SD}	Drain Diode Forward Voltage	V _{GS} =0V, I _S =20A	---	---	1.2	V
I_S	Maximum Continuous Drain to Source Diode Forward Current		---	---	20	A
I_{SM}	Maximum Pulsed Drain to Source Diode Forward Current		---	---	80	A
T_{rr}	Reverse Recovery Time	IF =10A, di/dt = 100A/μs	---	29	---	Ns
Q_{rr}	Reverse Recovery Charge		---	43	---	nc

Typical Characteristics: (T_C=25°C unless otherwise noted)




Figure 1 Output Characteristics




Figure 2 Transfer Characteristics




Figure 3 Rdson- Drain Current










Figure 4 Rdson-Junction Temperature


Figure 5 Gate Chare

Figure 6 Source- Drain Diode Forward

Figure 7 Capacitance vs Vds

Figure 8 Safe Operation Area

Figure 9 BV vs Junction Temperature

Figure 10 VGS(th) vs Junction Temperature




Figure 11 Normalized Maximum Transient Thermal Impedance

P-CH Electrical Characteristics: ($T_c=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\ \mu A$	-60	---	---	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{GS}=0V, V_{DS}=-60V$	---	---	-1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0A$	---	---	± 100	nA
On Characteristics³						
$V_{GS(th)}$	GATE-Source Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\ \mu A$	-1	-1.5	-2.2	V
$R_{DS(ON)}$	Drain-Source On Resistance	$V_{GS}=-10V, I_D=-12A$	---	80	90	m Ω
		$V_{GS}=-4.5V, I_D=-8A$	---	95	120	
G_{FS}	Forward Transconductance	$V_{DS}=-5V, I_D=-2A$	---	10	---	S
Dynamic Characteristics⁴						
C_{iss}	Input Capacitance	$V_{DS}=-30V, V_{GS}=0V, f=1MHz$	---	1600	---	pF
C_{oss}	Output Capacitance		---	90	---	
C_{rss}	Reverse Transfer Capacitance		---	75	---	

Switching Characteristics ^{„4}						
t_{d(on)}	Turn-On Delay Tim	V _{DS} =-30V,R _{GEN} =3 Ω , V _{GS} =-10V	---	11	---	ns
t_r	Rise Time		---	14	---	ns
t_{d(off)}	Turn-Off Delay Time		---	33	---	ns
t_f	Fall Time		---	13	---	ns
Q_g	Total Gate Charge	V _{GS} =-10V, V _{DS} =-30V, I _D =-12A	---	37.6	---	nC
Q_{gs}	Gate-Source Charge		---	4.3	---	nC
Q_{gd}	Gate-Drain Charge		---	7.2	---	nC
Drain-Source Diode Characteristics						
V_{SD}	Drain Diode Forward Voltage ³	V _{GS} =0V,I _S =-12A,T _J =25 °C	---	---	-1.2	V
I_S	Continuous Source Current ²	---	---	---	-12	A
T_{rr}	Reverse Recovery Time	T _J = 25 °C, IF =- 12A	---	-35	---	ns
Q_{rr}	Reverse Recovery Charge	di/dt = -100A/ μ s ^(Note3)	---	-38	---	nC

Notes:

1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. Surface Mounted on FR4 Board, $t \leq 10$ sec.
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$.
4. Guaranteed by design, not subject to production
5. E_{AS} condition: $T_J=25^\circ C, V_{DD}=-20V, V_G=-10V, L=1mH, R_g=25\Omega$

Typical Characteristics: ($T_C=25^\circ C$ unless otherwise noted)




Figure 1 Output Characteristics













Figure 2 Transfer Characteristics


Figure 3 Rdson- Drain Current

Figure 4 Rdson-Junction Temperature

Figure 5 Gate Charge

Figure 6 Source- Drain Diode Forward

Figure 7 Capacitance vs Vds

Figure 8 Safe Operation Area


Figure 9 Power De-rating

Figure 10 ID Current De-rating

Figure 11 Normalized Maximum Transient Thermal Impedance