



1

2

3



4

A



B

C



Technical requirements:

1、Unit: mm

2、Line diameter: 0.7

3、Material: carbon steel with nicked plated-meet ROHS

4、Style: straight cylinder double pin

5、Technics: high temperature of the 260℃ heat treatment

6、No be marked sizes is $\pm 0.25\text{mm}$ tolerances

7、No dirty surface,no bad material

8、Contact number: 13459252012、0592-5216722

9、Mode: F20-17-0.7-1.8UU

10、Salt spray test:

five precent salt spray test was met for 24hours

11、Packaging method: in bags-the minimum package is 500pcs

D

E

F

						碳钢线			厦门市芯网电子科技有限公司	
						阶段标记			重量	比例
标记	处数	分区	更改文件号	签名	年月日	s				2:1
设计										
校核										
批准										

1

2

3

4

A

B

C

D

E

F