



1

2

3

4



A



B

B

C



C

Technical requirements:

1、Unit: mm

2、Line diameter: 0.4

3、Material: carbon steel with nicked plated-meet ROHS

4、Style: straight cylinder inside double pin

5、Technics: high temperature of the 260℃ heat treatment

6、No be marked sizes is $\pm 0.25\text{mm}$ tolerances

7、No dirty surface,no bad material

8、Contact number: 0592-5216722

9、Mode: F6.6-10-0.4-1.2NUU

10、Salt spray test:

five precent salt spray test was met for 24hours

11、Packaging method: in bags-the minimum package is 2000pcs

D

D

E

E

F

F

						碳钢线			厦门市芯网电子科技有限公司	
标记	处数	分区	更改文件号	签名	年月日	阶段标记		重量	比例	
设计						s			3:1	
校核										
批准										

1

2

3

4