

承认书

APPROVAL SHEET

RoHS

客户名称

Customer Name:

客户料号

Customer P/N:

客户机种

Customer Product:

客户确认回复

Customer Approval



合格

PASSED



不合格

REJECTED

不合格原因

Reasons for the rejected

确认人

Confirm By

日期

Date

供应商: 东莞市长泰尔电子有限公司

SUPPLIER: DONG GUAN CHANG TAI ER ELECTRONIC., LTD.

产品类别:

Part Category

编码器

产品料号:

Part Number

ED08E420-FE18C9.0-A16-1002

产品摘要:

Part Note

Country origin of CHINA



ISO9001:2008/ISO14001



RoHS符合



TS16949

承办

Prepared By

工程部

2016.03.07

谢敏

品质
审核

Quality By

品管部

2016.03.07

郑丽芳

工程
审核

Engineering By

工程部

2016.03.07

喻钊

工程
核准

Approved By

工程部

2016.03.07

彭先炎

东莞工厂

DONG GUAN FACTORY

地址: 广东省东莞市厚街镇白濠工业区世纪路18号

Add:NO.18.Century Road ,Baihao Industrial Area,

HouJie Town,Dongguan City,Guangdong Province,China.

TEL: 0769-83085666、Dir:85911465、83085818、83085838

FAX: 0769-85911497、83085777

Http://www.changtaier.com

E-mail:webmaster@changtaier.com

泉州办事处

QUANZHOU OFFICE

地址: 福建省泉州市丰泽区东湖街道浔埔社区双江工业大楼A栋3楼

Add:Floor 3 ,Buid A,Shuang Jiang Industrial Edifice,Xu Pu Community,Dong Hu Street,
Feng Ze Borough ,QuanZhou City, FuJian Province.

TEL: 0595-22221511 TAC:13489209470




FAX: 0595-22251511

编码器规格书


ENCODER SPECIFICATIONS

1 一般事项 General information	
1-1 适用型号 Applicable models	ED08E 系列无开关型 ED08E Serial no have Switch type
1-2 使用环境温度 Usage environment temperature	- 20℃ ~ + 70℃
1-3 保存环境温度 Storage environment temperature	- 40℃ ~ + 70℃
1-4 测试条件 Test condition	温度: 5~35℃, 湿度: 45~85%HR Temperature:5~35℃, Moisture:45~85%HR
1-5 环保要求 Environmental requisition	本产品符合 RoHS 指令 This product is compliant with RoHS Directive
1-6 耐焊接热 Soldering heat-resistance	1、手工焊接温度最高 350℃±5℃, 3 秒; 2、自动焊接温度最高 260℃±5℃, 3 秒; 基板表面预热温度最高 100℃1 分钟以内; 3、以上过程均保证在 1 到 2 次; 4、不适用回流焊。 1. Soldering iron Max ,350℃±5℃ at 3 sec. 2. Auto soldering 260℃±5℃ max. at 3 sec. Preheating temperature of board surface: 100℃ max. at within 1 minutes. 3. To guarantee the above process at 1 or 2 times. 4. No apply the reflow soldering.
1-7 原产地 Country of origin	中国 China
2 构造 Construction	
2-1 外观 Appearance	各部件应完整, 无锈蚀、裂痕、电镀不良 Every part should finished, be not exist rust flaw crack and bad plating
2-2 寸法 Measurements	依照图面规定 Under conditions prescribed by design drawing.
3 机械性能 Mechanical characteristics	
3-1 全回转角度 Total rotational angle	300° ±5°
3-2 回转力矩 Rotational torque	70~400gf.cm (旋转速度: 60° /1 秒) 70~400gf.cm (Rotational velocity : 60° /1 Sec.)
3-3 回转止动强度 Rotational stopper strength	3Kgf.cm
3-4 定位数 Number of detent	16 个定位 16 Detents
3-5 切换角度 Change-Over angle	20° ±3°

3-6	轴压引强度 Pull-Push Strength of Shaft	≥10Kgf		
3-7	螺母锁紧强度 Nut tightening strength	≥10Kgf.cm		
3-8	轴摇晃度 Shaft wobble	在单个轴顶端施加压力 250gf，轴径向偏移量小于：0.7*轴长 L 尺寸/30mm On the tip of the single shaft exert pressure 250gf ， Shaft radial deviant be smaller than:0.7*shaft long L size/30mm		
4 电气性能 Electrical characteristics				
4-1	额定电压 Voltage rating	DC 5V		
4-2	额定电流 Current rating	1mA		
4-3	耐电压 Voltage proof	AC 300V 1 分钟以上（端子和本体之间，端子和轴芯之间） 1 Minute at AC 300V (Between terminal – case, Between terminal –shaft).		
4-4	最大使用电流 Maximum operating current	2.5mA		
4-6	绝缘抵抗 Insulation resistance	DC 250V 100MΩ 以上（端子和本体之间，端子和轴芯之间） 100MΩ min. At DC 250V (Between terminal – case, Between terminal –shaft).		
4-7	回转寿命 Rotational life	无负荷情况下每小时旋转 600 周，寿命 30,000 周，寿命后： 1、绝缘抵抗 10MΩ 以上 DC250V（端子和本体之间，端子和轴芯之间）； 2、耐电压 AC100V 1 分钟（端子和本体之间，端子和轴芯之间），绝缘阻抗无击穿； 3、回转力矩：满足第 3-2 项； 4、外观和结构无损坏。 30,000 cycles under no load circumstances by 600 r/h of rotation, afterlife cycle: 1. Insulation resistance:10MΩ min. At DC 250V. (Between terminal – case, Between terminal –shaft). 2. Withstanding voltage : AC 100V at 1 minute (Between terminal – case, Between terminal –shaft). No subversion on insulation resistance. 3. Rotational torque : Content item No. 3-2. 4. No damage on appearance and structure.		
5 防水性能 Waterproof standard characteristics				
6-1	防水标准 Waterproof standard	☒ 不适用 No apply ☐ 七级防水 编码器轴芯轴套置于水中 1 米深处，其它部件密封后暴露在标准大气压中，30 分钟后电位器内部未进水。 Grade -7 Of Waterproof standard Encoder's Shaft and Bush in water 1M deep, other component sealed after exposed to the standard atmosphere, after 30 minutes no water into the Encoder's inner.		
东莞市长泰尔电子有限公司 DONG GUAN CHANG TAI ER ELECTRONIC CO., LTD.		制 作 Designed By	审 核 Checked By	核 准 Approved By
		工程 部 2016.02.24 谢敏	工程 部 2016.02.24 喻钊	工程 部 2016.02.24 彭先炎




FD Shaft Style




L	15							
A	7.5							

FE Shaft Style




L	15	16.5	17	18	18	20	20	20.8	21.5
A	7	5.5	8	5.4	9	5.4	12	10	5.5

SC Shaft Style




L	6.5						
A	0.8						

FS Shaft Style



L	18							
A	9							

AH Shaft Style



L	13.5						
A	8.5						

未注尺寸公差	
$L \leq 1.0$ 时	± 0.1
$1.0 < L \leq 10$ 时	± 0.3
$10 < L \leq 30$ 时	± 0.5
$30 < L \leq 100$ 时	± 1.0

10			
9			
8	新增轴型	李昌平	2013. 10. 1
标记	变 更 内 容	改 图	日 期

click position								
	1	2	3	4	5	6	7	
	ED1(1-2)	0	1	1	0	0	1	1
	ED1(3-2)	1	1	0	0	1	1	0
	ED2(1-2)	1	1	0	1	0	0	1
	ED2(3-2)	0	0	1	1	1	1	0

东莞市长泰尔电子有限公司

比例	2.5:1	版本	1.8	设计	审核	批准
品名	ED08E□2O 组立图					
图号	ED08E□2O-□□□-A16-1002					