

## M12-SD-CC-IDC-4P-DCOD-M-STR-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 382 1410
Specification	M12-SD-CC-IDC-4P-DCOD-M-STR-SHLD
HARTING eCatalogue	<a href="https://b2b.harting.com/21033821410">https://b2b.harting.com/21033821410</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design
Element	Cable connector
Specification	Straight

### Version

Termination method	HARAX <sup>®</sup> connection technology
Gender	Male
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Locking type	Screw locking
Details	For Fast Ethernet applications only

### Technical characteristics

Conductor cross-section	0.14 mm <sup>2</sup>
Conductor cross-section	AWG 26
Wire outer diameter	≤1.6 mm
Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV
Pollution degree	3



Pushing Performance  
Since 1945

## Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	15
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 100$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521



**Pushing Performance**  
Since 1945

## Commercial data

Packaging size	1
Net weight	52.9 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140225343
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)