




CAD GENERATED DRAWING, DO NOT CHANGE BY HAND.

REV.	ECN. NO.	APPD.
B	BC-16-0036383	Nick Lin




- NOTES:
1. ALL DIMENSIONS ARE IN MILLIMETERS.
 2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
 3. 'FOXCONN' LOGO & DATE CODE & 'H95385-004' LOGO ARE LOCATED APPROXIMATELY, LARGER MARK
 4. MATERIAL:
 - BOLSTER PLATE: STAINLESS STEEL
 - SPRING PLATE: STAINLESS STEEL
 - CAPTIVE NUT: CARBON STEEL W/ N: PLATING OVERALL
 - COLLAR: CARBON STEEL W/ N: PLATING OVERALL
 - SMALL/ LARGE GUID POST: STAINLESS STEEL
 - CORNER STANDOFF: STAINLESS STEEL
 - SPRING STUD: STAINLESS STEEL
 - SPRING RIVET: STAINLESS STEEL
 - INSULATOR: INSULATING MATERIAL
 - DUST COVER: PC-ABS
 5. HARMFUL MATERIAL CONTROL PLEASE FOLLOW DOC. NO. 'EPI12'.
 6. THE CONCENTRATIONS OF B* AND C1 CAN SATISFY THE REQUIREMENT OF HALOGEN-FREE IN THE DOCUMENT 'EPI12'.
 7. PLEASE CONTACT FOXCONN SALES REPRESENTATIVE TO VERIFY PRODUCT DETAIL AND AVAILABILITY.




WNMEL60-80N00-EH	SKX-EP NON-FABRIC BOLSTER + DUST COVER
PART NUMBER	DESCRIPTION

X. ±	X. ° ± 1°	UNITS mm	NAME (INTENDED USE)	FOXCONN® FOXCONN INTERCONNECT TECHNOLOGY LIMITED.									
. X ± 0.50	. X ° ±	MAT'L	SKX-EP BOLSTER										
. XX ± 0.30	. XX ° ±		PART NO. (INTENDED USE)	CLASS: ☐ CONFIDENTIAL ☐ SECRET ☒ GENERAL									
. XXX ±	. XXX ° ±		WNMEL60-80N00-EH	TITLE: SKX-EP NARROW NON-FABRIC BOLSTER									
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED.			APPD: Nick Lin	DWG NO. : 351-0000-1392									
			CHKD: Dickie Huang Mac Peng	 <table><tr><td>SCALE</td><td>SHEET</td><td>REV.</td></tr><tr><td>1: 1</td><td>1/2</td><td>B</td></tr></table>			SCALE	SHEET	REV.	1: 1	1/2	B	
			SCALE				SHEET	REV.					
1: 1	1/2	B											
Q' TY	DR: Daryl Tan 9/3/16												

NO METAL OF BOLSTER PLATE
CAN BE EXPOSED.



OPPOSITE VIEW



- SOCKET P PLACEMENT ZONE
NO OTHER COMPONENT PLACEMENT ALLOWED.
0.0 MM HEIGHT RESTRICTION.
- SOCKET CAVITY
1.222 MM HEIGHT RESTRICTION.
- SOCKET PICK & PLACE CAP SKIRT ZONE
0.0 MM HEIGHT RESTRICTION.
- BOLSTER PLATE ZONE,
NO OTHER COMPONENT PLACEMENT ALLOWED,
0.0 MM HEIGHT RESTRICTION.

RECOMMENDED KEEP OUT ZONE

X. ±	X. ° ± 1°	UNITS	mm	NAME (INTENDED USE)	FOXCONN® FOXCONN INTERCONNECT TECHNOLOGY LIMITED. CLASS: ☐ CONFIDENTIAL ☐ SECRET ☒ GENERAL TITLE: SKX-EP SQUARE BOLSTER DWG NO.: 351-0000-1392 SCALE SHEET REV. N/A 2/2 B
. X ± 0.25	. X ° ±	MAT'L		SKX-EP BOLSTER	
. XX ± 0.13	. XX ° ±			PART NO. (INTENDED USE) WNMEL60-80N00-EH	
. XXX ±	. XXX ° ±	FINISH		APPD: Nick Lin	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED.				CHKD: Dickie Huang Mac Peng	
				DR: Daryl Tan 9/3/16	