









- NOTE:
1. MATERIAL
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL 94 V-0 FLAME RETARDANT, BLACK.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING: CONTACT AREA: 30u" Au OVER 50u" Ni UNDER ALL
SOLDER TAIL: 100u" MATTE PURE TIN OVER 50u" Ni UNDER.
 2. PRODUCT SPECIFICATION: GS-12-279.
 3. PRODUCT PACKAGING SPEC: GS-14-937.
 4. PART NUMBER 10034908-015LF MEETS EUROPEAN UNION
DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED
IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDER APPLICATION
WITH A CIRCUIT BOARD.
 5. PRODUCT MARKING ON HOUSING IN AREA SHOWN MEETS AFci SPECIFICATION: GS-24-007.
 6. A SYMBOL  WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN
MODIFIED WITH THE CURRENT DRAWING REVISION.




spec ref	*	dr	Eric Jiang	2013/03/18	projection	mm	size	A4	scale	1:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Sunny2 Liu	2016/04/12			ecn no	ELX-DG-22934-1	rel level	Released
		chr	Terris Liu	2016/05/20	product family	-	rel level	Released		
		appr	Pei-Ming Zheng	2016/05/24	product family	-	rel level	Released		
surface	linear	0.X	±0.50	Amphenol FCi	title	STRADDLE MOUNT TYPE	dwg no	10034908-015	rev	B
		0.XX	±0.25		cat. no.	-	Product - Customer Drw	sheet 1 of 2		
		0.XXX	±0.13							
	angular	0°	±2°							



PRODUCT NUMBER

10034908-015LF




RECOMMENDED PC BOARD LAYOUT



RECOMMENDED MATING BOARD LAYOUT



SECTION E-E

DETAIL A
SCALE 4:1DETAIL B
SCALE 4:1

spec ref	*	dr	Eric Jiang	2013/03/18	projection	mm	size	A4	scale	17:16
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Sunny2 Liu	2016/04/12			ecn no	ELX-DG-22934-1		
		chr	Terris Liu	2016/05/20			rel level	Released		
		appr	Pei-Ming Zheng	2016/05/24	product family					
surface	linear	0.X	±0.50	Amphenol FCi	title STRADDLE MOUNT TYPE POWER EDGE CARD		dwg no	10034908-015		rev B
		0.XX	±0.25							
		0.XXX	±0.13							
	angular	0°	±2°		cat. no.	*	Product - Customer Drw	sheet 2 of 2		