

Features

- Uni-directional ESD protection of one lines
- 3200Watts peak pulse power ($t_p = 8/20\mu s$)
- Working voltage: 18V
- Junction Capacitance: 270pF(Typ)
- Low clamping voltage
- Low leakage current
- IEC 61000-4-2 $\pm 30kV$ contact $\pm 30kV$ air
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning) 100A (8/20 μs)


Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation

Mechanical Data

- Package:DFN1610
- Molding compound flammability rating: UL 94V-0
- RoHS/WEEE Compliant

Schematic & PIN Configuration



Ordering Information

Part Number	Package	Marking	Packing	Reel Size
ESD56201D18-2/TR	DFN1610	 THW	10000 Tape & Reel	7 inches

Absolute Maximum Rating($T_A=25^{\circ}\text{C}$ unless otherwise Specified)

Rating	Symbol	Value	Units
Peak Pulse Power ($t_p=8/20\mu\text{s}$)	PPP	3200	Watts
Peak Pulse Current ($t_p=8/20\mu\text{s}$) (note1)	Ipp	100	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	30 30	kV
Lead Soldering Temperature	TL	260(10seconds)	$^{\circ}\text{C}$
Junction Temperature	TJ	-55 to + 125	$^{\circ}\text{C}$
Storage Temperature	Tstg	-55 to + 125	$^{\circ}\text{C}$


Electrical Characteristics($T_A=25^{\circ}\text{C}$ unless otherwise Specified)

Parameter	Symbol	Conditions	Min	Typical	Max	Units
Reverse Stand-Off Voltage	VRWM				18	V
Reverse Breakdown Voltage	VBR	$I_T=1\text{mA}$	19.5			V
Reverse Leakage Current	IR	$VRWM=18\text{V}, T=25^{\circ}\text{C}$			1	μA
Clamping Voltage	VC	$I_{PP}=100\text{A}, t_p=8/20\mu\text{s}$		32		V
Junction Capacitance	Cj	$V_R = 0\text{V}, f = 1\text{MHz}$		270		pF

Electrical Parameters ($T_A = 25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current

Note.: 8/20 μs pulse waveform.





Typical Characteristics($T_A=25^{\circ}\text{C}$ unless otherwise Specified)

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure3: Pulse Waveform






Figure 4: Clamping Voltage vs. I_{pp}





Outline Drawing – DFN1610



COMMON DIEMENSION (MM)			
PKG	DFN1610		
REF.	MIN.	NON.	MAX.
A	0.45	0.50	0.55
D	1.55	1.60	1.65
E	0.95	1.00	1.05
b	0.35	0.40	0.45
L	0.75	0.80	0.85
e	1.10BSC		
h	0.15	0.20	0.25