





REV.	REVISION DESCRIPTION	DATE	APPD


NOTES:

1. Rated voltage: 300V AC/DC
2. Rated current: 10A AC/DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temperature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
7. Materials: PBT UL94V-0(2)
8. Matched RoHS criteria



Circuits	Type	Dimension mm	
		A	B
2	VYH-2AS	6.50	12.30
3	VYH-3AS	13.00	18.80
4	VYH-4ASM	19.50	25.30

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: VYH-AS	TITLE: 6.50 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 19/08/01
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DATE: 19/08/01	PART NO: VYH-AS
FINISH:		CHKD: Wu Hui	DATE: 19/08/01
DRAWING NO: GC-VYH-AS		APPD: Ren An De	DATE: 19/08/01
		SCALE: N/A	PAGE: 1/2
		UNITS: mm	REV.: A




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 10A AC DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
 - 7. Materials: PBT UL94V-0(2)
 - 8. Matched RoHS criteria

Circuits	Type	Dimension mm	
		A	B
2X2	VYH-4AS	6.50	12.30
2X3	VYH-6AS	13.00	18.80

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: VYH-AS	TITLE: 6.50 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 19/08/01
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DATE: 19/08/01	PART NO:
FINISH:		CHKD: Wu Hui	DATE: 19/08/01
DRAWING NO:		APPD: Ren An De	DATE: 19/08/01
		SCALE: N/A	PAGE: 2/2
		UNITS: mm	REV.: A




NOTES:

1. Rated voltage: 300V AC. DC
2. Rated current: 10A AC DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temprature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
7. Materials: Nylon UL94V-0(2)
8. Matched RoHS criteria

Circuits	Type	Dimension mm	
		A	B
2	VYH-2Y	6.50	12.30
3	VYH-3Y	13.00	18.80
4	VYH-4YM	19.50	25.30


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: VYH-Y		TITLE: 6.50 mm Pitch Housing	
. XX: ± 0.15	. X° : $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:19/08/01	PART NO:	
. XXX: ± 0.01	. XX° : $\pm 1.0^{\circ}$			SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:19/08/01	PAGE: 1/2	
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm	REV. : A



- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 10A AC DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
 - 7. Materials: Nylon UL94V-0(2)
 - 8. Matched RoHS criteria

Circuits	Type	Dimension mm	
		A	B
2X2	VYH-4Y	6.50	12.30
2X3	VYH-6Y	13.00	18.80

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: VYH-Y		TITLE: 6.50 mm Pitch Housing	
. XX: ± 0.15	. X° : $\pm 2.0^{\circ}$			PART NO:	
. XXX: ± 0.01	. XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:19/08/01	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:19/08/01	PAGE: 2/2	
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD


NOTES


Available in 02、03、04、06 Circuits.

Match with VYH-Y series housing

Material : Nylon UL94V-0(2).

Circuits	Type	Dimension mm	
		A	B
2	VYH-2S	6.50	10.30
3	VYH-3S	13.00	16.80
4	VYH-4S	19.50	23.30

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: VYH-S		TITLE: 6.50 mm Pitch Housing	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Yuan Jun Rong	DATE:21/03/18	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21/03/18		
DRAWING NO:		APPD:Ren An De	DATE:21/03/18	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in VYH-Y Series Housing.

Accepts AWG #26~16 Wire Range.

Material : Phosphor Bronze .

Finish: Tin plated.

Qty/Reel: 4,000 PCS.

Thickness: 0.25 mm.

TYPE	Dimension mm				适用线规
	A1	B1	A2	B2	AWG
VYH-T-G	4.2	4.1	2.7	3.1	#20-16
VYH-T	3.5	3.5	2.2	2.2	#26-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: VYH-T		TITLE: 6.50 mm Pitch Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/08/01	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:21/08/01	PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV.: A