



1. FIGURE AND DIMENSIONS (视图及尺寸)



| Main technical indicators (主要技术指标) |                                |
|------------------------------------|--------------------------------|
| 1. Mating (插拔次数)                   | 1000                           |
| 2. Working Temperature (温度)        | -50~+70°                       |
| 3. IP Rating (防护级别)                | IP 50                          |
| 5. Rated voltage (额定电压)            | 400V                           |
| 6. Rated Current (额定电流)            | 5                              |
| 7. Shell material (壳体材质)           | Zinc alloy nickel plated/锌合金镀镍 |
| 8. Pin Material (插针材料)             | Copper gilding(铜镀金)            |
| 9. Insulation resistance (绝缘电阻)    | >100MΩ                         |
| 10. Insulator material (绝缘体材料)     | 橡胶黑木                           |
| 11. Salt spray test (盐雾测试)         | >48H                           |

| Sum up (总结)                 |                                                                   |
|-----------------------------|-------------------------------------------------------------------|
| Series (系列)                 | GX12                                                              |
| Shell style/model (外壳样式/型号) | GX12:Fixed socket, front and rear panel mount type/固定式插座, 前后面板安装型 |
| Button (按键)                 | 1 button(1个按键)                                                    |
| Termination type (终止类型)     | Male solder(公板接)                                                  |
| Line diameter awg(线材直径)     | -                                                                 |
| Cable diameterΦ (电缆直径)      | -                                                                 |
| Match plug(匹配插头)            | -                                                                 |

|        |  |      |  |          |                                       |                                                                                     |
|--------|--|------|--|----------|---------------------------------------|-------------------------------------------------------------------------------------|
| 版本     |  |      |  | TITLE    | DRAWING NO.                           | REV.                                                                                |
| REVA4  |  |      |  |          | FG. GX16. P10. CAL                    | A0                                                                                  |
| REVA3  |  |      |  |          |                                       |                                                                                     |
| REVA2  |  |      |  |          |                                       |                                                                                     |
| REVA1  |  |      |  |          |                                       |                                                                                     |
| DRAW   |  | DATE |  | PART NO. | SHEET                                 |  |
| CHECK  |  | DATE |  |          |                                       |                                                                                     |
| APPR'D |  | DATE |  | USE      | XKB INDUSTRIAL PRECISION CO., LIMITED |                                                                                     |