





SIZE	Part Num.	Threading	Packaging
25	8655MHRA2511KCLF	UNC 4.40	KIT (see note)



NOTES:

Material and finish: Zinc die-cast
Nickel plated

Cable strain relief: Polycarbonate (UL94V-0)

Jackscrew : Metal

Temperature range: -40°C to 120°C

Cable diameter: 4,0 to 13,0mm

Attenuation factor: >40 dB between 30MHz and 1 GHz

Covers screwing force (max): 100 Ncm

Jackscrew screwing force (max): 50 Ncm

Packaging notes :


- Kit : 1 set of components in a plastic bag
necessary to realise 1 cable termination
- 100 plastic bags max per carton box.

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

DESIGNATION	REP.	09	15	25	37	50
COVER BOTTOM	1			1		
JACKSCREW	2	1			2	
STRAIN RELIEF	3			2		
COVER TOP	4			1		
SCREW POZIDRIVE	5			2		

1 KIT
SEE PACKAGING NOTE

spec ref		dr		A Parrenin	2011/04/15	projection 	mm 	size	A3	scale	3:2
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	J Dalibard	2015/10/29	ecn no			ELX-F-22316-1			
		chr	J Dalibard	2015/10/29				rel level	Released		
		appr	Aymeric Soudy		2015/10/29	product family					
surface ✓ ISO 1302	linear	0.X	± /			title	D-SUB METAL SHELLS (ANGLED) METAL JACK SCREWS WITHOUT FCI LOGO	dwg no	10117915		rev C
		0.XX	± /								
		0.XXX	± /								
		angular	0°	± / °		www.fci.com	cat. no.	Product - Customer Drw		sheet 1 of 2	

1



2

3

4



SIZE	Part Num.	Threading	Packaging
9	8655MHRA0911KCLF	UNC 4.40	KIT (see note)

SIZE	Part Num.	Threading	Packaging
15	8655MHRA1511KCLF	UNC 4.40	KIT (see note)



SIZE	Part Num.	Threading	Packaging
37	8655MHRA3711KCLF	UNC 4.40	KIT (see note)

SIZE	Part Num.	Threading	Packaging
	8655MHRA5011KCLF	UNC 4.40	KIT (see note)



spec ref				dr	A Parrenin	2011/04/15	projection 	mm 	size	A3	scale	1:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	J Dalibard	2015/10/29			ecn no	ELX-F-22316-1		
				chr	J Dalibard	2015/10/29			rel level Released			
				appr	Aymeric Soudy	2015/10/29						product family
surface ISO 1302	linear	0.X	± /		title	D-SUB METAL SHELLS (ANGLED) METAL JACK SCREWS WITHOUT FCI LOGO			dwg no	10117915		rev C
		0.XX	± /									
		0.XXX	± /									
	angular	0°	± / °									



Copyright FCI.