

MICRO-ISO AUTOMOTIVE LOW PROFILE RELAY

CV-N RELAYS (ACVN)



Micro ISO 1 Form A type


FEATURES

- Low profile automotive relays for Micro-ISO terminal
- Compact and high-capacity load switching
- Plastic sealed type

TYPICAL APPLICATIONS

- Headlights
- Magnetic clutches
- Radiator fans
- Blowers
- Fog lamps
- Tail lights
- Heaters
- Defoggers
- Horns
- · Condenser fans, etc.

ORDERING INFORMATION



TYPES

Contact arrangement	Coil voltage	Protective construction	Mounting classification	Part No.
1 Form A 12 V DC Plast		Plastic sealed type	Micro ISO plug-in type	ACVN51012

Note: Please use "ACVN**2**" to order with resistor inside type. (Asterisks " * " should be filled in from ORDERING INFORMATION.) Standard packing; Carton: 50 pcs.; Case: 200 pcs.

RATING

1. Coil data

Nominal coil voltage	Pick-up voltage* (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power (at 20°C 68°F)	Usable voltage range (at 85°C 185°F)
12V DC	Max. 7.0 V DC (Initial)	Min. 0.5 V DC (Initial)	66.7 mA, 74.7 mA (with resistor)	180 Ω , 160.7 Ω (with resistor)	0.8 W, 0.9 W (with resistor)	10 to 16V DC

CV-N (ACVN)

2. Specifications

Characteristics	Item		Specifications		
Contact	Arrangement		1 Form A		
	Contact resistance (Initial)		Typ $3m\Omega$ (By voltage drop 6V DC 1A)		
	Contact voltage drop (Initial)		N.O.: Max. 0.5 V (By voltage drop 14 V DC 35 A)		
	Contact material		Ag alloy (Cadmium free)		
Rating	Nominal switching capacity (resistive load)		N.O.: 35 A 14V DC		
	Max. carrying current (at 85°C 185°F, continuous)		N.O.: 20 A 14V DC		
	Nominal operating power (at 20°C 68°F)		0.8 W, 0.9 W (with resistor inside type)		
	Min. switching capacity (resistive load)*1 (at 20°C 68°F)		1 A 14V DC		
	Insulation resistance (Initial)		Min. 20 MΩ (at 500V DC, Measurement at same location as "Breakdown voltage" section.)		
	Breakdown voltage (Initial)	Between open contacts	500 Vrms for 1 min. (Detection current: 10mA)		
Electrical characteristics		Between contacts and coil	500 Vrms for 1 min. (Detection current: 10mA)		
	Operate time (at nominal voltage) (at 20°C 68°F)		Max. 10ms (excluding contact bounce time) (Initial)		
	Release time (at nominal voltage) (at 20°C 68°F)		Max. 10ms (Initial)		
	Shock resistance	Functional	Min. 100 m/s² {10G} (Half-wave pulse of sine wave: 11ms; detection time: 10μs)		
Mechanical		Destructive	Min. 1,000 m/s² {100G} (Half-wave pulse of sine wave: 6ms)		
characteristics	Vibration resistance	Functional	10 Hz to 100 Hz, Min. 44.1 m/s² {4.5G} (Detection time: 10μs)		
		Destructive	10 Hz to 500 Hz, Min. 44.1 m/s² {4.5G}, Time of vibration for each direction; X, Y, Z direction: 4 hours		
Expected life	Mechanical		Min. 10 ⁶ (at 120 cpm)		
	Electrical		<resistive load=""> Min. 10⁵ (at nominal switching capacity, operating frequency: 2s ON, 2s OFF)</resistive>		
			<motor load=""> Min. 3×10^5 (at 84 A (inrush), 18 A (steady), 14 V DC), Operating frequency: 2s ON, 5s OFF</motor>		
			<lamp load=""> Min. 2 × 10⁵ (at 84 A (inrush), 12 A (steady), 14 V DC), Operating frequency: 1s ON, 14s OFF</lamp>		
Conditions	Conditions for operation, transport and storage*2		Ambient temperature: -40°C to +85°C -40°F to +185°F*³, Humidity: 5% R.H. to 85% R.H. (Not freezing and condensing at low temperature), air pressure: 86 to 106kPa		
Mass			Approx. 12 g .42 oz		

Notes:


*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

*2. The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. Refer to "6. Usage, Storage and Transport Conditions" in AMBIENT ENVIRONMENT section in Relay Technical Information.


*3. Please inquire if you will be using the relay in a high temperature atmosphere.

REFERENCE DATA


1. Coil temperature rise Point measured: Inside the coil Contact carrying current: 20A Coil applied voltage: 12V, 14V, 16V Ambient temperature: 85°C 185°F




2. Distribution of pick-up and drop-out voltage Sample: ACVN51012, 20pcs



3. Distribution of operate and release time Sample: ACVN51012, 20pcs.



4. Ambient temperature and operating voltage range




5.-(1) Electrical life test (Lamp load)

Sample: ACVN51012, 3pcs.


Load: 60W×2 (halogen lamp load), Inrush: 84A/

steady: 12A Switching frequency: ON 1s, OFF 14s Ambient temperature: 85°C 185°F


Circuit




Load current waveform Inrush current: 84A, steady current: 12A



Change of pick-up and drop-out voltage



Change of contact resistance




CV-N (ACVN)

5.-(2) Electrical life test (Motor load) Sample: ACVN51012, 3pcs. Inrush: 80A/steady: 18A


radiator fan motor (motor free) Switching frequency: ON 1s, OFF 4s Ambient temperature: 85°C 185°F

Circuit




Load current waveform


Inrush current: 80A, steady current: 18A



Change of pick-up and drop-out voltage



Change of contact resistance



DIMENSIONS (mm inch)


Download **CAD Data** from our Web site.


1. Micro ISO plug-in type






External dimensions





Schematic (Bottom view)



Tolerance Dimension: Max. 1mm .039 inch: ±0.1 ±.004 1 to 3mm .039 to .118 inch: ±0.2 ±.008 Min. 3mm .118 inch: $\pm 0.3 \pm .012$

Note: Intervals between terminals is measured at A surface level.

For Cautions for Use, see Relay Technical Information.