



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **White**

Primary Product Material: **Nylon**

Number of Positions: **15**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # 1-640388-5
15P MTA156 HDR ASSY RN STR F/L











TE Part # 644958-1
15P MTA156 HDR ASSY,R/A,OMIT



TE Part # 1-640445-5
15P MTA156 HDR ASSY FL/STR SNL



 TE Part # 1-640385-5 15P MTA156 HDR ASSY SQ R/A	 TE Part # 1-640383-5 15P MTA156 HDR ASSY STR SQ SN	 TE Part # 1-643067-2 12P MTA156 MOLDED COVER	 TE Part # 4-640426-5 15P MTA156 CONN ASSY 18AWG ORA
 TE Part # 1-640384-5 15P MTA156 HDR ASSY STR RND SN	 TE Part # 4-640428-5 15P MTA156 CONN ASSY 22AWG RED	 TE Part # 1-640387-5 15P MTA156 HDR ASSY SQ R/A	 TE Part # 1-640251-5 15P SL156 HSG W/O LCK RAMP
 TE Part # 4-640600-5 15P MTA156 CONN ASSY 20AWG LF	 TE Part # 1-644752-5 15P MTA156 HDR ASSY SQ STR F/L	 TE Part # 1-640389-5 15P MTA156 HDR ASSY SQ R/A F/L	 TE Part # 1-770996-5 15P SL 156 HSG W/TABS W/O LR
 TE Part # 4-643819-5 15P MTA156 CONN ASSY 22AWG LF	 TE Part # 4-640427-5 15P MTA156 CONN ASSY 20AWG YEL	 TE Part # 4-641435-5 15P MTA156 CONN ASSY ORNG	 TE Part # 641533-1 02P MTA156 CONN HSG,END CAP

Also in the Series | MTA 156

 Connector Caps & Covers(89)	 Connector Contacts(4)	 Connector Hardware(2)	 Insertion & Extraction Tools(1)
--	--	--	--



PCB Headers & Receptacles(317)



Rectangular Power Connectors(691)



Standard Rectangular Connectors(336)

Customers Also Bought



TE Part #59803-1
MAINTENANCE TOOL




TE Part #59804-1
MAINTENANCE TOOL




TE Part #3-643818-5
05P MTA156 CONN ASSY 20AWG YEL



TE Part #3-747579-4
SHLDNG FERRULE, PLTD, BULK PKG



TE Part #5-1437720-7
T01-CRIMP-S05=TRIAD




TE Part #640309-3
UMNL PIN 12-10 PTPPHBZ



TE Part #4-640599-2
12P MTA156 CONN ASSY 18AWG ORA



TE Part #350552-3
UMNL PIN 20-14 PTPPHBZ L/P



TE Part #643067-9
09P MTA156 MOLDED COVER



TE Part #NB20384001
VERSAFIT-3/16-6-SP

Documents

Product Drawings

15P MTA156 MOLDED COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-643067-5_P.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-643067-5_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-643067-5_P.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_1-643067-5_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-643067-5_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-643067-5_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English