



- NOTES 1 Rotation examples of ref No. ① and No. ⑦ are shown.  
2 The recommended clamp torque of ref. No. ⑩ : 0.2 to 0.3N・m.  
3 Across flats of hexagon hole of ref. No. ⑩ : 1.27

5	PHOSPHOR BRONZE	NICKEL PLATING	11	CHLOROPRENE RUBBER	(BLACK)
4	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	10	STEEL	NICKEL PLATING JIS B 1177 HEXAGON SOCKET SET SCREW M2.6×0.45×2
3	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	9	BRASS	NICKEL PLATING JIS B 1111 PAN HEAD MACHINE SCREW M3×0.5×8
2	COPPER ALLOY	SILVER PLATING 2μ min.	8	POLYACETAL	
1	ALUMINUM ALLOY	NICKEL PLATING	7	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED
			6	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI	15. 09. 14	DRAWING NO.	EDC-119152-00-00
		CHECKED : HY. KOBAYASHI	15. 09. 14	PART NO.	JRC16BP-10SA
		DESIGNED : KN. IKEHARA	15. 09. 14	CODE NO.	CL114-0301-0-00
		DRAWN : KN. IKEHARA	15. 09. 14		