

MODIFIED HEADER MTMM SERIES

SPECIFICATIONS

For complete specifications see www.samtec.com?MTMM

Insulator Material:
Black Liquid Crystal Polymer



Terminal Material:
Phosphor Bronze

Plating:
Sn or Au over 50µ" (1,27µm) Ni

Current Rating:
3A @ 80°C ambient


Operating Temp Range:
-55°C to +105°C with Tin;
-55°C to +125°C with Gold

RoHS Compliant:
Yes

Processing:


Max Processing Temp:
230°C for 60 seconds, or
260°C for 20 seconds 3x
Lead-Free Solderable:
Yes

Mates with:
CLT, SQT, SQW, ESQT,
TLE, SMM, MMS, TCSD




Choice of
single, double or
quad row

Specify post
height in (0,13mm)
.005" increments



ALSO AVAILABLE



Paste In Hole (PIH) processing.
Contact Samtec ASP Group.



MTMM	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	POST HEIGHT	OPTION
		01 thru 50	Specify LEAD STYLE from chart.	-G = 20µ" (0,51µm) Gold post Gold flash on tail -S = 30µ" (0,76µm) Gold post, Matte Tin on tail -T = Matte Tin	-S = Single Row -D = Double Row -Q = Quad Row	- "XXX" = Post Height in inches (0,13mm) .005" increments Example: -070 = (1,78mm) .070"	- "XXX" = Polarized Position Specify position of omitted pin
		<p>- S & -Q - D</p>					

LEAD STYLE	OAL
-02	(6,48) .255
-03	(7,67) .302
-04	(8,20) .323
-05	(9,58) .377
-06	(10,08) .397
-07	(11,58) .456
-08	(12,09) .476
-09	(13,59) .535
-10	(14,10) .555
-11	(15,09) .594
-12	(15,60) .614
-13	(17,09) .673
-14	(19,08) .751
-15	(21,08) .830

Note: This Series is non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM