

Operation: 立貼式 & 四脚小型 轻触开关

RoHS Compliant

LTEM NO.:TS-1808S-□ (Series)

(L4.2×W3.3×H2.5mm TACT-SWITCH)

表面貼裝 SMT

正向操作

精密部品 NICETY


可靠 STABILIZE

適合環保 RoHS





Technical parameter

PROJECT	LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating	0.25A, 24V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
	There No Load	115,000 Cycles	100,000 Cycles
Durable Performance	Rated Load	100,000 Cycles	850,000 Cycles
	Storage temp.	-40℃~+85℃(Operating Temp:)	
	Operating Force	1.6 / 2.6N. (1N.=100gram-force)	
	Heat Rrsistance	IR Reflow:255℃,5sec. Manual:350℃,3sec.	

CIRCUIT DIAGRAM



Unit:mm



P.C.B LAYOUT

