





9-1532140-4 Product Details



9-1532140-4

TE Internal Number: 9-1532140-4



SMB RF Connectors

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector - RF
- Plug
- Miniature
- Applies To Coaxial Cable
- Coupler Style = Threaded

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- [Gender](#) = Plug
- Connector Series = Miniature
- [Grade](#) = Commercial
- Thread Size = 4.83 [.190]-32
- Coupling Nut Style = Hex
- Dielectric Material = Fluoropolymer

Mechanical Attachment:

- [Panel Mount Retention](#) = Without
- Safety Wire Holes = Without

Electrical Characteristics:

- [Connector Impedance](#) (Ω) = 50

Termination Features:

- [Coaxial Cable Termination Type](#) = Solder

Dimensions:

- Cable Jacket Diameter (mm [in]) = 2.21 [0.087]

Body Features:

- Coupler Style = Threaded
- [Body Style](#) = Straight
- [Pin Protection](#) = Without
- [Body Plating](#) = Silver
- Body Material = Brass

Contact Features:

- [Center Contact Plating](#) = Gold per MIL-G-45204, Type II, Grade C, Class 1

Configuration Features:

- Preloaded = Yes
- Solder Lug = Without
- Environmental Protection = Without
- Solderless = No

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Coaxial Cable

Other:

- Brand = Microdot

Feedback

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



