




REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN APVD
	L1	REVISED	PER	ECN-22-185264	18NOV2022	RK MF



- 1 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 2 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 3 .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
- 4 .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
- 5 PRELIMINARY PART – NOT RELEASED FOR PRODUCTION.
- 6 HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

	△	△	1.684	1.600	16	34	4-103322-7	
	△	△	1.184	1.100	11	24	4-103322-6	
	△	△	.584	.500	5	12	4-103322-5	
		△	.284	.200	2	6	4-103322-4	
	△	△	.084	—	—	2	4-103322-3	
		△	3.984	3.900	39	80	4-103322-2	
	△	△	.484	.400	4	10	4-103322-1	
		△	3.984	3.900	39	80	4-103322-0	
△		△	3.884	3.800	38	78	3-103322-9	
△		△	3.784	3.700	37	76	3-103322-8	
△		△	3.684	3.600	36	74	3-103322-7	
△	SUPERSEDED BY 8-146250-6		△	3.584	3.500	35	72	3-103322-6
△		△	3.484	3.400	34	70	3-103322-5	
△		△	3.384	3.300	33	68	3-103322-4	
△		△	3.284	3.200	32	66	3-103322-3	
△		△	3.184	3.100	31	64	3-103322-2	
△		△	3.084	3.000	30	62	3-103322-1	
△		△	2.984	2.900	29	60	3-103322-0	
△		△	2.884	2.800	28	58	2-103322-9	
△		△	2.784	2.700	27	56	2-103322-8	
△		△	2.684	2.600	26	54	2-103322-7	
△		△	2.584	2.500	25	52	2-103322-6	
△		△	2.484	2.400	24	50	2-103322-5	
△		△	2.384	2.300	23	48	2-103322-4	
△		△	2.284	2.200	22	46	2-103322-3	
△		△	2.184	2.100	21	44	2-103322-2	
△		△	2.084	2.000	20	42	2-103322-1	
△	SUPERSEDED BY 7-146250-0		△	1.984	1.900	19	40	2-103322-0
△		△	1.884	1.800	18	38	1-103322-9	
△		△	1.784	1.700	17	36	1-103322-8	
△		△	1.684	1.600	16	34	1-103322-7	
△		△	1.584	1.500	15	32	1-103322-6	
△		△	1.484	1.400	14	30	1-103322-5	
△		△	1.384	1.300	13	28	1-103322-4	
△		△	1.284	1.200	12	26	1-103322-3	
△		△	1.184	1.100	11	24	1-103322-2	
△		△	1.084	1.000	10	22	1-103322-1	
△	SUPERSEDED BY 6-146250-0		△	.984	.900	9	20	1-103322-0
△		△	.884	.800	8	18	103322-9	
△		△	.784	.700	7	16	103322-8	
		△	.684	.600	6	14	103322-7	
		△	.584	.500	5	12	103322-6	
		△	.484	.400	4	10	103322-5	
		△	.384	.300	3	8	103322-4	
		△	.284	.200	2	6	103322-3	
		△	.184	.100	1	4	103322-2	
△	SUPERSEDED BY 5-146250-1		△	.084	—	—	2	103322-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.MARTINELLI CHK JOHN KNITTLE APVD B. FLINCHBAUGH	15OCT92 23NOV92 23NOV92	TE Connectivity	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	ASSY, HEADER, B/A, MOD II, DOUBLE ROW, .100 X .100 C/L, VERTL WITH .025 SQ POSTS	SIZE	CAGE CODE
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APPLICATION SPEC	RESTRICTED TO	100779	103322
MATERIAL POST: COPPER ALLOY	FINISH SEE TABLE	WEIGHT —	A1	SCALE 4:1	SHEET 1 OF 1
CUSTOMER DRAWING			REV L1		