

## SUMMARY

### # Wires



|             |    |
|-------------|----|
| Low voltage | 12 |
|-------------|----|

*Image is for illustrative purpose only*

|                  |                                    |
|------------------|------------------------------------|
| Series           | 2T                                 |
| Termination type | Female solder                      |
| IP rating        | 68                                 |
| AWG wire size    | 30.00 - 22.00                      |
| Cable Ø          | 8.10 - 8.50 mm                     |
| Status           | active                             |
| Matching parts   | <a href="#">FGG.2T.312.CLAC85Z</a> |

### Download

[Request a quote](#)  
[Eplan](#)  
[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | PH*: Free receptacle, cable collet and nut for fitting a bend relief                                                          |
| Keying            | 1 key (alpha=0; plug: male contacts, receptacle: female contacts)                                                             |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Variant           | Z : Nut for fitting a bend relief                                                                                             |
| Weight            | 30.15 g                                                                                                                       |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 2T.312 : 12 Low Voltage   |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 7 Amps                    |

### Specifications

|                          |                               |
|--------------------------|-------------------------------|
| Contact Type:            | Solder                        |
| Contact Dia.:            | 0.7 mm (0.028in)              |
| Bucket Dia.:             | 0.8 mm (0.031in)              |
| Max. Solid Conductor:    | 0.34 mm <sup>2</sup> (AWG 22) |
| Max. Stranded Conductor: | 0.34 mm <sup>2</sup> (AWG 22) |
| R (max):                 | 6.1 mOhm                      |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Vtest (contact-shell): 1350 V (AC), 1910 V (DC)  
Vtest (contact-contact): 1250 V (AC), 1770 V (DC)

## Others

Endurance (Shell): >3000 mating cycles  
Temp (min / max): -55°C / +200°C  
Humidity (max): <=95% [at 60 deg C /140 F]  
Resistance to vibration: 15 g [10 Hz - 2000 Hz]  
Shock Resistance: 100 g [ 6 ms]  
Climatical Category: 50/175/21  
Shielding efficiency (min): 75 dB (at 10 MHz)  
Shielding efficiency (min): 40 dB (at 1 GHz)  
Salt Spray Corrosion: >1000 hr

---

## DRAWINGS



## Dimensions

|     | A    | L    |
|-----|------|------|
| mm. | 15   | 51   |
| in. | 0,59 | 2,01 |

---

## RECOMMENDED BY LEMO

### Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

*LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*