

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	29MAY'09	S.C	J.K
	B	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z









FIG 1. ⁵
RECOMMENDED PANEL OPENING DIMENSION
TOLERANCES: ±0.13



- NOTE;
- THIS HOUSING ACCEPTS TAB TERMINAL:
-TAB CONTACT: 177917-□ (AWG#16-#20)
177916-□ (AWG#22-#26)
 - MATING CONN. P/N
-PLUG HSG: 2005247-□
-REC CONTACT: 177915-□ (AWG#16-#20)
: 177914-□ (AWG#22-#26)
 - APPLICABLE DOUBLE LOCK PLATE:
177918-1(V-0) OR □-368590-1(V-2,GWT)
*IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y
 - GENERAL TOLERANCES: ±0.3
 - APPLICATOIN PANEL THICKNESS: 0.8~2.0 (SEE FIG 1.)
 - INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
 - EDGE OF THICKNESS MAY MUST NOT ROUND FOR MOLDED PANEL.
 - MATERIAL: PA66, UL94V-0.
COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC
MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED
IN IEC 60335-1, SECTION 30(GWT).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM		TE Connectivity			
DIMENSIONS: mm		CHK BW KANG					
		APVD JK SONG		NAME PDL 2P CAP HSG 3.96mm P/M (GWT)			
		PRODUCT SPEC 108-5410					
		APPLICATION SPEC 114-5175					
		WEIGHT -					
MATERIAL 		FINISH -		SIZE A3	CAGE CODE 00779	DRAWING NO C-2005249	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 1	OF 1	REV B